BALLUFF

Photoelectric sensor BOS 08E with background suppression

Precise object detection in a mini-housing


Focused bright light spot for easy setup
Parameterization with IO-Link

Rugged, IP67 stainless steel housin



Two configuration methods – this is the new background suppression of the BOS 08E sensor family. The built-in potentiometer allows you to conveniently and quickly set the range from 7 to 30 mm. The IO-Link version offers even more advantages such as setting the range, hysteresis, and switching modes. The smallest Balluff sensor with background suppression is now available for space restricted applications.






BALLUFF

OIO-Link

OIO-Link







IO-Link functions: operating distance and hysteresis adjustable, switching type and switching modes selectable, diagnostic functions

Accessories			
Description	Mounting cuff	Mounting brackets	
		for sensors and clamps M8	
Hole diameter	Ø 8 mm		
	BAM00A2	BAM009U	
Material	PA 6	Anodized aluminum	

Connector				
Туре	2 m cable PUR (black)	2 m cable PUR (black)		
	with M8 connector,	with M8 connector,		
	3-pin (straight)	3-pin (right-angle)		
	BCC02M8	BCC02ML		