

# CERTIFICATE OF PRODUCT CERTIFICATION

## TYPE II CQC CERTIFICATION

CERTIFICATE NO.: CQC21107296687

Valid from: Aug.04,2021

Valid until: Aug.04,2031

**NAME AND REGISTERED ADDRESS OF THE APPLICANT** Balluff GmbH  
Schurwaldstrasse 9 D-73765 Neuhausen, Germany

**NAME AND REGISTERED ADDRESS OF THE MANUFACTURER** Balluff GmbH  
Schurwaldstrasse 9 D-73765 Neuhausen, Germany

**NAME AND LOCATION OF THE FACTORY** Balluff-Elektronika Kft  
H-8417,Cseteny Locational number: 042/40, Hungary

**PRODUCT NAME, MODEL AND SPECIFICATION** Limit Switch  
BNS... , BSE... ; Ui:250V;Uimp: BSE 30.0/ BSE 61/ BSE 85: 4 kV, BSE 69.1/ BSE 70.1/ BSE 86 / BSE 79/ BSE 73.1/ BSE 74.1: 2.5 kV;Ith : BSE 30.0/ BSE 61/ BSE 85: 6A, BSE 69.1/ BSE 70.1/ BSE 86 / BSE 79: 5A, BSE 73.1/ BSE 74.1: 0.1A;Ue/Ie: BSE30.0/BSE61/BSE85: AC-13:250V/2A, DC-12: 220V/0.5 A, BSE79/BSE69.1/BSE70.1: AC-13:250V/5A, DC-12: 220V/5A, BSE73.1/BSE74.1:AC-13: 250V/0.1A, DC-12: 220V/0.1A, BSE86: AC-13: 250V/5A, DC-12: 125V/0.3A;Utilization Category : AC-13,DC-12;Levels of packaging Protection : IP67;See the Appendix

**THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS** GB/T 14048.5-2017

**TYPE OF CERTIFICATION SCHEMES** Type Testing of Product + Follow up Factory Inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC12-000001-2020.  
The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

The certificate information is available through the QR code below or CNCA's website: [www.cnca.gov.cn](http://www.cnca.gov.cn)



SIGN BY

陈昕

SIGNATURE

谢肇煦



CHINA QUALITY CERTIFICATION CENTRE



# 产品认证证书

## II型自愿认证

证书编号: CQC21107296687

发证日期: 2021年08月04日

有效期至: 2031年08月04日

委托人名称	Balluff GmbH
及注册地址	Schurwaldstrasse 9 D-73765 Neuhausen, Germany
制造商名称	Balluff GmbH
及注册地址	Schurwaldstrasse 9 D-73765 Neuhausen, Germany
生产企业名称	Balluff-Elektronika Kft
及生产地址	H-8417,Cseteny Locational number: 042/40, Hungary
产品名称和系列、规格、型号	限位开关 BNS... , BSE... ;Ui:250V;Uimp: BSE 30.0/ BSE 61/ BSE 85: 4 kV, BSE 69.1/ BSE 70.1/ BSE 86 / BSE 79/ BSE 73.1/ BSE 74.1: 2.5 kV;Ith : BSE 30.0/ BSE 61/ BSE 85: 6A, BSE 69.1/ BSE 70.1/ BSE 86 / BSE 79: 5A, BSE 73.1/ BSE 74.1: 0.1A;Ue/Ie: BSE30.0/BSE61/BSE85: AC-13:250V/2A, DC-12: 220V/0.5 A, BSE79/BSE69.1/BSE70.1: AC-13:250V/5A, DC-12: 220V/5A, BSE73.1/BSE74.1:AC-13: 250V/0.1A, DC-12: 220V/0.1A, BSE86: AC-13: 250V/5A, DC-12: 125V/0.3A;使用类别 : AC-13,DC-12;外壳防护等级 : IP67;型号解释见附件
产品标准和技术要求	GB/T 14048.5-2017
认证模式	产品型式试验+获证后监督

上述产品符合 CQC12-000001-2020 认证规则的要求, 特发此证。

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

可通过扫描下方二维码或登录国家认监委网站(www.cnca.gov.cn)查验证书信息



授权签字人

签发

陈昕

谢肇煦



中国质量认证中心

