

BMF Magnetic Field Sensors

HOSE CLAMPS



Piston diameter	BMF 303-HW-59 with hose clamp BMF Gr. _		BMF 305-HW-24 with hose clamp BMF Gr. _		BMF 21-HW-11 with hose clamp BMF Gr. _		BMF 32 series with hose clamp BMF Gr. _		BMF 307-HW-112 with hose clamp BMF Gr. _		BMF 10E-HW-19 with hose clamp BMF Gr. _	
≤ 8 mm			0	BAM00N2					0	BAM00N2		
8...10 mm	1	BAM00N3	1	BAM00N3	1	BAM00N3	1	BAM00N3	1	BAM00N3	2	BAM00N4
12 mm	2	BAM00N4	1	BAM00N3	1	BAM00N3	1	BAM00N3	1	BAM00N3	2	BAM00N4
16 mm	2	BAM00N4	1	BAM00N3	2	BAM00N4	2	BAM00N4	1	BAM00N3	3	BAM00N5
20 mm	2	BAM00N4	2	BAM00N4	2	BAM00N4	2	BAM00N4	2	BAM00N4	3	BAM00N5
25 mm	2	BAM00N4	2	BAM00N4	2	BAM00N4	2	BAM00N4	2	BAM00N4	3	BAM00N5
32 mm	3	BAM00N5	3	BAM00N5	3	BAM00N5	3	BAM00N5	3	BAM00N5	4	BAM00N6
40 mm	4	BAM00N6	4	BAM00N6	4	BAM00N6	4	BAM00N6	4	BAM00N6	5	BAM00N7
50 mm	5	BAM00N7	5	BAM00N7	5	BAM00N7	5	BAM00N7	5	BAM00N7	6	BAM00N8
63 mm	6	BAM00N8	6	BAM00N8	6	BAM00N8	6	BAM00N8	6	BAM00N8	8	BAM00NA
70 mm	8	BAM00NA	8	BAM00NA	8	BAM00NA	8	BAM00NA	8	BAM00NA		
80 mm	7	BAM00N9	7	BAM00N9	7	BAM00N9	7	BAM00N9	7	BAM00N9		
90 mm	10	BAM01TC	10	BAM01TC	10	BAM01TC	10	BAM01TC	10	BAM01TC	10	BAM01TC
100 mm	9	BAM01F4	9	BAM01F4	9	BAM01F4	9	BAM01F4	9	BAM01F4	9	BAM01F4