

**Superior code reading characteristics for the harsh conditions of everyday industry**

## BVS HS-P, INDUSTRIAL HANDHELD BARCODE READER

The BVS HS-P handheld barcode readers read all common 2D, 1D and stacked barcodes fast and reliably. As HDW variant Highresolution codes (to 2.5 mil for 1D) as well as large areas (up to Letter format / DIN A4) can be read up to 70 cm away. The DPW variant is optimized to solve up to 80% of all Direct part mark applications. The reader offers industry standard IP 65 protection and can withstand repeated drops on concrete from a distance of up to 2 m. This ensures reliable use in harsh environments in addition to logistics and warehousing. The wireless models with Bluetooth give users maximum mobility up to 100 m from the base station. The operator-friendly and ergonomic reader is intuitive and simple to use.

CE





## HANDHELD BARCODE READER BVS HS-P

Direct-Part-Marking (DP)	BVS001T	BVS001Z
High-Density (HD)	BVS001U	BVS001Y
Illuminant lighting	LED, white	LED, white
Illuminant aimer	Laser, red, Class 2	Laser, red, Class 2
Interface	RS232/USB	RS232/USB Bluetooth 2.0/2.4 GHz
Connection type	Cable	Wireless
Enclosure Type per IEC 60529	IP65	IP65
Fall protection	> 50 drops; 2 m to concrete	> 50 drops; 2 m to concrete

## ZUBEHÖR

	BAM02JM	BAM02HM	BAM02JC	
Description	Powersupply, 12V, EU/IEC for base station	Base station for bluetooth reader	Height adjustable positioner	

## CONNECTORS

	BAM02HY	BAM02HZ	BAM02J0	BAM02J3
Description	RS232, straight, 1.8 m	RS232, coiled, 2.4 m	USB A, straight, 2 m	USB A, coiled, 2.4 m

## Services



You can rely on our support over the entire life cycle of our products and solutions: Including the design and planning of your projects, testing and setup on site, and training and support. For more information, visit us online at [www.balluff.com/en/de/service/services/](http://www.balluff.com/en/de/service/services/)