

EMVA 1288 Data Sheet m1354


This data sheet describes the specification according to the standard 1288 Release 4.0 Linear issued on 21 June 2021 for "Characterization and Presentation of Specification Data for Image Sensors and Cameras" by the European Machine Vision Association (EMVA), published at <https://www.emva.org/standards-technology/emva-1288/> with proprietary extensions from AEON. The measurements were performed with the AEON ACC2b 14x1 color, Release 9, 13.11.2020, SN 0066(Balluff), software version 3.3.

Measurements performed by Product Development Vision, Balluff GmbH

Type of data presented	Single
Vendor	Balluff GmbH
Model	BVS CA-GW1-0164AG
Serial number	GW000045
Sensor diagonal	22.63 mm
Lens category	TFL-Mount
Resolution	8000 × 2048, 12 bit
Offset/size channels	0 × 0/ 8000 × 2048
Pixel size (h×v)	2.74 μm × 2.74 μm
Sensor	IMX901
Sensor type	CMOS
Shutter type	Global
Overlap cap.	Overlapping
Max. frame rate	0.0 Hz
Interface type	GigEVision

Nr.	Centroid/FWHM	Gain, blacklevel	t_{exp} (ms)
1	542.0/33.9 nm	0.0dB, 0.1	2.00


Optional data measured: None




Summary Sheet for Operation Point 1 at a Wavelength of 542 nm

Type of data	Single	Gain, black-level	0.0dB, 0.1
Exposure control	By irradiance	Environmental temperature	20.9°C
Exposure time	2.000 ms	Camera body temperature	34.7°C
Frame rate	92.4 Hz	Internal temperature(s)	44.2°C, 38.0°C
Data transfer mode	Mono12p	Wavelength, centr., FWHM	542 nm, 33.9 nm

Photon Transfer



Signal-to-Noise Ratio



Quantum efficiency

η 63.3%

Overall system gain

K 0.4273 DN/e⁻

1/ K 2.340 e⁻/DN

Temporal dark noise

σ_d 2.51 e⁻

$\sigma_{y, \text{dark}}$ 1.11 DN

Signal-to-noise ratio

SNR_{max} 94.9

39.5 dB

1/SNR_{max} 1.054 %

Absolute sensitivity threshold

$\mu_{e, \text{min}}$ 3.15 e⁻

$\mu_{e, \text{min. area}}$ 0.419 e⁻/μm²

Saturation capacity

$\mu_{e, \text{sat}}$ 9004 e⁻

$\mu_{e, \text{sat. area}}$ 1199 e⁻/μm²

Dynamic range

DR 2862

69.13 dB

Spatial nonuniformities

DSNU₁₂₈₈ 0.369 e⁻

DSNU_{1288.col} 0.024 e⁻

DSNU_{1288.row} 0.031 e⁻

DSNU_{1288.pix} 0.367 e⁻

PRNU₁₂₈₈ 0.343 %

PRNU_{1288.col} 0.021 %

PRNU_{1288.row} 0.109 %

PRNU_{1288.pix} 0.325 %

Linearity error

LE 0.15%

Dark current

$\mu_{c, \text{mean}}$ 1.23E+00 e⁻/s

$\mu_{c, \text{var}}$ 2.33E+00 e⁻/s