

EMVA 1288 Data Sheet m1305


This data sheet describes the specification according to the standard 1288 Release 4.0 Linear issued on 21 June 2021 for "Characterization and Presentation of Specification Data for Image Sensors and Cameras" by the European Machine Vision Association (EMVA), published at <https://www.emva.org/standards-technology/emva-1288/> with proprietary extensions from AEON. The measurements were performed with the AEON ACC2b 14x1 color, Release 9, 13.11.2020, SN 0066(Balluff), software version 3.2.

Measurements performed by Product Development Vision, Balluff GmbH

Type of data presented	Single
Vendor	Balluff GmbH
Model	BVS CA-GV1-0204AG
Serial number	GV000103
Sensor diagonal	17.48 mm
Lens category	C-Mount
Resolution	4512 × 4512, 12 bit
Offset/size channels	0 × 0/ 4512 × 4512
Pixel size (h×v)	2.74 μm × 2.74 μm
Sensor	IMX541
Sensor type	CMOS
Shutter type	Global
Overlap cap.	Overlapping
Max. frame rate	0.0 Hz
Interface type	GigEVision

Nr.	Centroid/FWHM	Gain, blacklevel	t_{exp} (ms)
1	542.0/33.9 nm	0.0dB, 0.1	2.00


Optional data measured: None




Summary Sheet for Operation Point 1 at a Wavelength of 542 nm

Type of data	Single	Gain, black-level	0.0dB, 0.1
Exposure control	By irradiance	Environmental temperature	23.4°C
Exposure time	2.000 ms	Camera body temperature	32.7°C
Frame rate	18.3 Hz	Internal temperature(s)	45.2°C, 35.0°C
Data transfer mode	Mono12p	Wavelength, centr., FWHM	542 nm, 33.9 nm

Photon Transfer



Signal-to-Noise Ratio



Quantum efficiency

η 67.3%

Overall system gain

K 0.4145 DN/e⁻

$1/K$ 2.412 e⁻/DN

Temporal dark noise

σ_d 2.18 e⁻

$\sigma_{y, \text{dark}}$ 0.950 DN

Signal-to-noise ratio

SNR_{max} 97.6

39.8 dB

$1/\text{SNR}_{\text{max}}$ 1.025 %

Absolute sensitivity threshold

$\mu_{e, \text{min}}$ 2.85 e⁻

$\mu_{e, \text{min, area}}$ 0.379 e⁻/μm²

Saturation capacity

$\mu_{e, \text{sat}}$ 9516 e⁻

$\mu_{e, \text{sat, area}}$ 1268 e⁻/μm²

Dynamic range

DR 3343

70.48 dB

Spatial nonuniformities

DSNU₁₂₈₈ 0.587 e⁻

DSNU_{1288, col} 0.051 e⁻

DSNU_{1288, row} 0.033 e⁻

DSNU_{1288, pix} 0.584 e⁻

PRNU₁₂₈₈ 0.305 %

PRNU_{1288, col} 0.061 %

PRNU_{1288, row} 0.016 %

PRNU_{1288, pix} 0.299 %

Linearity error

LE 0.19%

Dark current

$\mu_{c, \text{mean}}$ 6.53E-01 e⁻/s

$\mu_{c, \text{var}}$ 6.30E-01 e⁻/s