


EMVA 1288 Data Sheet m0637

This datasheet describes the specification according to the standard 1288 for “Characterization and Presentation of Specification Data for Image Sensors and Cameras of the European Machine Vision Association (EMVA)” (see www.standard1288.org or the *Zenodo EMVA 1288 community*) release 3.0 with proprietary extensions from AEON. The measurements were performed with the AEON ACC3 Release 6, 18.07.2016, SN 0005(MatrixVision) . The performance parameters and estimated accuracy of the measurements are described in the technical report for the instrument, its calibration in the corresponding specification and calibration report.

Measurements performed by T.Renner, Matrix Vision GmbH



Vendor	MATRIX VISION
Model	mvBlueCOUGAR-X100fG
Serial number	GX017984
Sensor diagonal	6.27 mm
Lens category	C-Mount
Resolution	728 × 544, 12 bit
Pixel size	6.90 μm × 6.90 μm
Sensor	IMX287
Sensor type	CMOS
Shutter type	Global
Overlap capabilities	Overlapping
Maximum frame rate	150.7 Hz
Interface type	GigE Vision

Type of data presented	Single
Operation point 1, (page 3)	
Wavelength centroid	536.0 nm
Wavelength FWHM	31.0 nm
Gain, black-level	0dB, 0.1
Optional data measured	
None	



EMVA 1288 Summary Sheet for Operating Point 1

Type of data	Single	Gain, black-level	0dB, 0.1
Exposure control	By irradiance	Environmental temperature	25.2°C
Exposure time	7.00 ms	Camera body temperature	37.3°C
Frame rate	32.0 Hz	Internal temperature(s)	—
Data transfer mode	Mono12	Wavelength, centr., FWHM	536 nm, 31.0 nm



Quantum efficiency

η 62.5%

Overall system gain

K 0.187 DN/e⁻

$1/K$ 5.340 e⁻/DN

Temporal dark noise & DSNU

$\sigma_{y,\text{dark}}$ 0.70 DN

DSNU₁₂₈₈ 0.23 DN

σ_d 3.39 e⁻

DSNU₁₂₈₈ 1.23 e⁻

Signal-to-noise ratio & PRNU

SNR_{max} 146

43.3 dB

7.2 bit

$1/\text{SNR}_{\text{max}}$ 0.69 %

PRNU₁₂₈₈ 0.44 %

Nonlinearity

LE 0.31%

LE_{min} -0.25%

LE_{max} 0.36%

Sensitivity & saturation

$\mu_{p,\text{min}}$ 6.80 p

0.143 p/ μm^2

$\mu_{p,\text{sat}}$ 33945 p

713 p/ μm^2

$\mu_{e,\text{min}}$ 4.26 e⁻

0.089 e⁻/ μm^2

$\mu_{e,\text{sat}}$ 21231 e⁻

446 e⁻/ μm^2

Dynamic range

DR 4989

74.0 dB

12.3 bit

Dark current

$\mu_{c,\text{mean}}$ -3.2 DN/s

$\mu_{c,\text{mean}}$ -17.0 e⁻/s

$\mu_{c,\text{var}}$ 22.5 e⁻/s