


EMVA 1288 Summary Sheet

This datasheet describes the specification according to the standard 1288 for Characterization and Presentation of Specification Data for Image Sensors and Cameras of the European Machine Vision Association (EMVA)(see www.standard1288.org). The measurements were performed with an AEON ACC3 RGB Release 3, 20.01.2104, SN 0005() . The performance parameters and estimated accuracy of the measurements are described in the technical report for the instrument, its calibration in the corresponding calibration report.



Vendor	MATRIX VISION
Model	mvBlueCOUGAR-X102eGE
Serial number	GX001880
Sensor diagonal	8.69 mm
Lens category	C-Mount
Resolution	1280 × 1024, 10 bit
Pixel size	5.30 μm × 5.30 μm
Sensor type	CMOS
Shutter type	Global
Overlap capabilities	Overlapping
Maximum frame rate	45.5 Hz
Interface type	GigE Vision

Type of data presented	Single
Operation point 1, (page 4)	
Wavelength centroid	534.2 nm
Wavelength FWHM	30.9 nm
Gain, offset	Gain = 0dB, Offset = 17.0
Operation point 2, (page 16)	
Wavelength centroid	629.5 nm
Wavelength FWHM	13.1 nm
Gain, offset	Gain = 0dB, Offset = 17.0
Optional data measured	
None	



EMVA 1288 Summary Sheet for Operating Point 1



Type of data	Single	Gain, offset	Gain = 0dB, Offset = 17.0
Exposure time	5.0 ms	Environmental temperature	26.1°C
Frame rate	0.0 Hz	Camera temperature	25.9°C
Data transfer mode	Mono10	Wavelength, centr., FWHM	534 nm, 30.9 nm



Quantum efficiency	
η	0.556
Gain	
K (DN/e)	0.127
$1/K$ (e/DN)	7.879
Dark noise & DSNU	
σ_d (DN)	2.94
σ_0 (e)	23.0
DSNU ₁₂₈₈ (DN)	5.41
DSNU ₁₂₈₈ (e)	42.64
Signal-to-noise ratio & PRNU	
SNR _{max}	88
SNR _{max} (dB)	38.9
SNR _{max} (bits)	6.5
$1/\text{SNR}_{\text{max}}$ (%)	1.14
PRNU ₁₂₈₈ (%)	1.711
Nonlinearity	
LE (%)	0.68
Sensitivity & saturation	
$\mu_{p,\text{min}}$ (p)	42.5
$\mu_{e,\text{min}}$ (e)	23.6
$\mu_{p,\text{sat}}$ (p)	13863
$\mu_{e,\text{sat}}$ (e)	7714
Dynamic range	
DR	326
DR (dB)	50.3
DR (bit)	8.4
Dark current	
$\mu_{c,\text{mean}}$ (DN/s)	109.30
$\mu_{c,\text{mean}}$ (e/s)	861.13
$\mu_{c,\text{var}}$ (e/s)	366.99

EMVA 1288 Summary Sheet for Operating Point 2

Type of data	Single	Gain, offset	Gain = 0dB, Offset = 17.0
Exposure time	5.0 ms	Environmental temperature	26.1°C
Frame rate	0.0 Hz	Camera temperature	25.9°C
Data transfer mode	Mono10	Wavelength, centr., FWHM	630 nm, 13.1 nm



Quantum efficiency	
η	0.585
Gain	
K (DN/e)	0.122
$1/K$ (e/DN)	8.185
Dark noise & DSNU	
σ_d (DN)	2.94
σ_0 (e)	23.9
DSNU ₁₂₈₈ (DN)	5.41
DSNU ₁₂₈₈ (e)	44.30
Signal-to-noise ratio & PRNU	
SNR _{max}	89
SNR _{max} (dB)	39.0
SNR _{max} (bits)	6.5
$1/\text{SNR}_{\text{max}}$ (%)	1.12
PRNU ₁₂₈₈ (%)	2.198
Nonlinearity	
LE (%)	0.59
Sensitivity & saturation	
$\mu_{p,\text{min}}$ (p)	42.0
$\mu_{e,\text{min}}$ (e)	24.6
$\mu_{p,\text{sat}}$ (p)	13519
$\mu_{e,\text{sat}}$ (e)	7910
Dynamic range	
DR	322
DR (dB)	50.2
DR (bit)	8.3
Dark current	
$\mu_{c,\text{mean}}$ (DN/s)	—
$\mu_{c,\text{mean}}$ (e/s)	—
$\mu_{c,\text{var}}$ (e/s)	—