


EMVA 1288 Data Sheet m0970

This datasheet describes the specification according to the standard 1288 release 3.1 for "Characterization and Presentation of Specification Data for Image Sensors and Cameras" issued on December 30, 2016 by the European Machine Vision Association (EMVA), published at www.standard1288.org and the *zenodo EMVA 1288 community* with proprietary extensions from AEON. The measurements were performed with the AEON ACC3 Release 6, 26.11.2016, SN 0005(MatrixVision.

Measurements performed by T.Renner, Matrix Vision GmbH

| | | | |
|------------------|----------------------|------------------------------------|----------|
| Vendor | MATRIX VISION | Type of data presented | Single |
| Model | mvBlueCOUGAR-XD108aC | Operation point 1 (page 5) | |
| Serial number | GX225283 | Wavelength centroid | 468.0 nm |
| Sensor diagonal | 11.05 mm | Wavelength FWHM | 20.0 nm |
| Lens category | C-Mount | Gain, black-level | 0dB, 0.1 |
| Resolution | 2856 × 2848, 12 bit | Operation point 2 (page 19) | |
| Pixel size (h×v) | 2.74 μm × 2.74 μm | Wavelength centroid | 535.0 nm |
| Sensor | IMX546 | Wavelength FWHM | 31.0 nm |
| Sensor type | CMOS | Gain, black-level | 0dB, 0.1 |
| Shutter type | Global | Operation point 3 (page 33) | |
| Overlap cap. | Overlapping | Wavelength centroid | 630.0 nm |
| Max. frame rate | 14.6 Hz | Wavelength FWHM | 13.0 nm |
| Interface type | GigE Vision | Gain, black-level | 0dB, 0.1 |
| | | Optional data measured | None |




Summary Sheet for Operation Point 1 at a Wavelength of 468 nm

| | | | |
|--------------------|---------------|---------------------------|-----------------|
| Type of data | Single | Gain, black-level | 0dB, 0.1 |
| Exposure control | By irradiance | Environmental temperature | 21.1°C |
| Exposure time | 1.50 ms | Camera body temperature | 36.4°C |
| Frame rate | 12.0 Hz | Internal temperature(s) | — |
| Data transfer mode | BayerRG12 | Wavelength, centr., FWHM | 468 nm, 20.0 nm |


Photon Transfer

Photon transfer m0970, 468 nm, 31.01.2022



Signal-to-Noise Ratio

SNR m0970, 468 nm, 31.01.2022



Quantum efficiency

η 45.1%

Overall system gain

K 0.410 DN/e⁻

$1/K$ 2.438 e⁻/DN

Temporal dark noise

σ_d 2.46 e⁻

$\sigma_{y,\text{dark}}$ 1.05 DN

Signal-to-noise ratio

SNR_{max} 98

39.8 dB

6.6 bit

$1/\text{SNR}_{\text{max}}$ 1.02 %

Absolute sensitivity threshold

$\mu_{p,\text{min}}$ 6.90 p

$\mu_{p,\text{min,area}}$ 0.919 p/ μm^2

$\mu_{e,\text{min}}$ 3.11 e⁻

$\mu_{e,\text{min,area}}$ 0.414 e⁻/ μm^2

Saturation capacity

$\mu_{p,\text{sat}}$ 21278 p

$\mu_{p,\text{sat,area}}$ 2834 p/ μm^2

$\mu_{e,\text{sat}}$ 9587 e⁻

$\mu_{e,\text{sat,area}}$ 1277 e⁻/ μm^2

Dynamic range

DR 3083

69.8 dB

11.6 bit

Spatial nonuniformities

DSNU₁₂₈₈ 0.32 e⁻

0.13 DN

PRNU₁₂₈₈ 0.50 %

Linearity error

LE_{min} -0.13%

LE_{max} 0.19%

Dark current

$\mu_{c,\text{mean}}$ 1.2 ± 0.0 e⁻/s

0.48 DN/s


$\mu_{c,\text{var}}$ 4.1 ± 0.8 e⁻/s

T_d — °C


Summary Sheet for Operation Point 2 at a Wavelength of 535 nm

| | | | |
|--------------------|---------------|---------------------------|-----------------|
| Type of data | Single | Gain, black-level | 0dB, 0.1 |
| Exposure control | By irradiance | Environmental temperature | 21.2°C |
| Exposure time | 1.50 ms | Camera body temperature | 36.0°C |
| Frame rate | 12.0 Hz | Internal temperature(s) | — |
| Data transfer mode | BayerRG12 | Wavelength, centr., FWHM | 535 nm, 31.0 nm |

Photon Transfer



Signal-to-Noise Ratio



Quantum efficiency

η 51.4%

Overall system gain

K 0.410 DN/e⁻

$1/K$ 2.438 e⁻/DN

Temporal dark noise

σ_d 2.46 e⁻

$\sigma_{y,\text{dark}}$ 1.05 DN

Signal-to-noise ratio

SNR_{max} 98

39.8 dB

6.6 bit

$1/\text{SNR}_{\text{max}}$ 1.02 %

Absolute sensitivity threshold

$\mu_{p,\text{min}}$ 6.04 p

$\mu_{p,\text{min,area}}$ 0.805 p/ μm^2

$\mu_{e,\text{min}}$ 3.11 e⁻

$\mu_{e,\text{min,area}}$ 0.414 e⁻/ μm^2

Saturation capacity

$\mu_{p,\text{sat}}$ 18717 p

$\mu_{p,\text{sat,area}}$ 2493 p/ μm^2

$\mu_{e,\text{sat}}$ 9622 e⁻

$\mu_{e,\text{sat,area}}$ 1282 e⁻/ μm^2

Dynamic range

DR 3099

69.8 dB

11.6 bit

Spatial nonuniformities

DSNU₁₂₈₈ 0.38 e⁻

0.16 DN

PRNU₁₂₈₈ 0.51 %

Linearity error

LE_{min} -0.50%

LE_{max} 0.85%

Dark current

$\mu_{c,\text{mean}}$ 1.2 ± 0.0 e⁻/s

0.49 DN/s

$\mu_{c,\text{var}}$ 1.6 ± 0.5 e⁻/s


T_d — °C

Summary Sheet for Operation Point 3 at a Wavelength of 630 nm

| | | | |
|--------------------|---------------|---------------------------|-----------------|
| Type of data | Single | Gain, black-level | 0dB, 0.1 |
| Exposure control | By irradiance | Environmental temperature | 21.2°C |
| Exposure time | 1.50 ms | Camera body temperature | 35.9°C |
| Frame rate | 12.0 Hz | Internal temperature(s) | — |
| Data transfer mode | BayerRG12 | Wavelength, centr., FWHM | 630 nm, 13.0 nm |


Photon Transfer

Photon transfer m0970, 630 nm, 31.01.2022



Signal-to-Noise Ratio

SNR m0970, 630 nm, 31.01.2022



Quantum efficiency

η 37.8%

Overall system gain

K 0.410 DN/e⁻

$1/K$ 2.442 e⁻/DN

Temporal dark noise

σ_d 2.47 e⁻

$\sigma_{y,\text{dark}}$ 1.05 DN

Signal-to-noise ratio

SNR_{max} 99

39.9 dB

6.6 bit

$1/\text{SNR}_{\text{max}}$ 1.01 %

Absolute sensitivity threshold

$\mu_{p,\text{min}}$ 8.24 p

$\mu_{p,\text{min,area}}$ 1.097 p/ μm^2

$\mu_{e,\text{min}}$ 3.12 e⁻

$\mu_{e,\text{min,area}}$ 0.415 e⁻/ μm^2

Saturation capacity

$\mu_{p,\text{sat}}$ 25818 p

$\mu_{p,\text{sat,area}}$ 3439 p/ μm^2

$\mu_{e,\text{sat}}$ 9770 e⁻

$\mu_{e,\text{sat,area}}$ 1301 e⁻/ μm^2

Dynamic range

DR 3135

69.9 dB

11.6 bit

Spatial nonuniformities

DSNU₁₂₈₈ 0.41 e⁻

0.17 DN

PRNU₁₂₈₈ 0.56 %

Linearity error

LE_{min} -0.51%

LE_{max} 0.24%

Dark current

$\mu_{c,\text{mean}}$ 1.2 ± 0.0 e⁻/s

0.48 DN/s

$\mu_{c,\text{var}}$ 3.0 ± 0.8 e⁻/s

T_d — °C