EMVA 1288 Data Sheet m0881

This datasheet describes the specification according to the standard 1288 release 3.1 for "Characterization and Presentation of Specification Data for Image Sensors and Cameras" issued on December 30, 2016 by the European Machine Vision Association (EMVA), published at `www.standard1288.org` and the *zenodo EMVA 1288 community* with proprietary extensions from AEON. The measurements were performed with the AEON ACC3 Release 6, 26.11.2016, SN 0005(MatrixVision.

Measurements performed by T.Renner, Matrix Vision GmbH

Vendor	MATRIX VISION
Model	BVS-CA-GT1-0246ZG
Serial number	GT000007
Sensor diagonal	19.30 mm
Lens category	C-Mount
Resolution	5328 × 4608, 12 bit
Pixel size (h×v)	2.74 μm × 2.74 μm
Sensor	IMX530
Sensor type	CMOS
Shutter type	Global
Overlap cap.	Overlapping
Max. frame rate	33.5 Hz
Interface type	GigE Vision

Type of data presented	Single
Operation point 1 (page 3)	
Wavelength centroid	535.0 nm
Wavelength FWHM	31.0 nm
Gain, black-level	0dB, 0.1
Optional data measured	
None	



Summary Sheet for Operation Point 1 at a Wavelength of 535 nm

Type of data	Single	Gain, black-level	0dB, 0.1
Exposure control	By irradiance	Environmental temperature	24.0°C
Exposure time	1.00 ms	Camera body temperature	38.1°C
Frame rate	10.0 Hz	Internal temperature(s)	—
Data transfer mode	Mono12p	Wavelength, centr., FWHM	535 nm, 31.0 nm

Photon Transfer



Signal-to-Noise Ratio



Quantum efficiency

η	67.2%

Overall system gain

K	0.419 DN/e$^-$
$1/K$	2.389 e$^-$/DN

Temporal dark noise

σ_d	2.23 e$^-$
$\sigma_{y.\mathrm{dark}}$	0.98 DN

Signal-to-noise ratio

$\mathrm{SNR}_{\max}$	96
	39.6 dB
	6.6 bit
$1/\mathrm{SNR}_{\max}$	1.04 %

Absolute sensitivity threshold

$\mu_{p.\mathrm{min}}$	4.30 p
$\mu_{p.\mathrm{min.area}}$	0.572 p/μm^2
$\mu_{e.\mathrm{min}}$	2.89 e$^-$
$\mu_{e.\mathrm{min.area}}$	0.385 e$^-$/μm^2

Saturation capacity

$\mu_{p.\mathrm{sat}}$	13713 p
$\mu_{p.\mathrm{sat.area}}$	1827 p/μm^2
$\mu_{e.\mathrm{sat}}$	9222 e$^-$
$\mu_{e.\mathrm{sat.area}}$	1228 e$^-$/μm^2

Dynamic range

DR	3192
	70.1 dB
	11.6 bit

Spatial nonuniformities

DSNU_{1288}	0.85 e$^-$
	0.36 DN
PRNU_{1288}	0.67 %

Linearity error

$\mathrm{LE}_{\min}$	-0.34%
$\mathrm{LE}_{\max}$	0.47%

Dark current

$\mu_{c.\mathrm{mean}}$	4.3 ± 0.0 e$^-$/s
	1.79 DN/s
$\mu_{c.\mathrm{var}}$	4.7 ± 0.0 e$^-$/s
T_d	— °C