


## EMVA 1288 Data Sheet m0973

This datasheet describes the specification according to the standard 1288 release 3.1 for "Characterization and Presentation of Specification Data for Image Sensors and Cameras" issued on December 30, 2016 by the European Machine Vision Association (EMVA), published at [www.standard1288.org](http://www.standard1288.org) and the *zenodo EMVA 1288 community* with proprietary extensions from AEON. The measurements were performed with the AEON ACC3 Release 6, 26.11.2016, SN 0005(MatrixVision.

Measurements performed by T.Renner, Matrix Vision GmbH

Vendor	MATRIX VISION	Type of data presented	Single
Model	mvBlueCOUGAR-XD105dG	<b>Operation point 1 (page 3)</b>	
Serial number	GX225275	Wavelength centroid	535.0 nm
Sensor diagonal	8.82 mm	Wavelength FWHM	31.0 nm
Lens category	C-Mount	Gain, black-level	0dB, 0.1
Resolution	2472 × 2064, 12 bit	<b>Optional data measured</b>	
Pixel size (h×v)	2.74 μm × 2.74 μm	None	
Sensor	IMX547		
Sensor type	CMOS		
Shutter type	Global		
Overlap cap.	Overlapping		
Max. frame rate	23.3 Hz		
Interface type	GigE Vision		




## Summary Sheet for Operation Point 1 at a Wavelength of 535 nm

Type of data	Single	Gain, black-level	0dB, 0.1
Exposure control	By irradiance	Environmental temperature	22.1°C
Exposure time	1.50 ms	Camera body temperature	36.2°C
Frame rate	22.0 Hz	Internal temperature(s)	—
Data transfer mode	Mono12	Wavelength, centr., FWHM	535 nm, 31.0 nm


### Photon Transfer

Photon transfer m0973, 535 nm, 31.01.2022



### Signal-to-Noise Ratio

SNR m0973, 535 nm, 31.01.2022



#### Quantum efficiency

$\eta$  67.5%

#### Overall system gain

$K$  0.427 DN/e<sup>-</sup>

$1/K$  2.343 e<sup>-</sup>/DN

#### Temporal dark noise

$\sigma_d$  2.36 e<sup>-</sup>

$\sigma_{y,\text{dark}}$  1.05 DN

#### Signal-to-noise ratio

SNR<sub>max</sub> 96

39.7 dB

6.6 bit

$1/\text{SNR}_{\text{max}}$  1.04 %

#### Absolute sensitivity threshold

$\mu_{p,\text{min}}$  4.45 p

$\mu_{p,\text{min,area}}$  0.593 p/μm<sup>2</sup>

$\mu_{e,\text{min}}$  3.00 e<sup>-</sup>

$\mu_{e,\text{min,area}}$  0.400 e<sup>-</sup>/μm<sup>2</sup>

#### Saturation capacity

$\mu_{p,\text{sat}}$  13785 p

$\mu_{p,\text{sat,area}}$  1836 p/μm<sup>2</sup>

$\mu_{e,\text{sat}}$  9310 e<sup>-</sup>

$\mu_{e,\text{sat,area}}$  1240 e<sup>-</sup>/μm<sup>2</sup>

#### Dynamic range

DR 3099

69.8 dB

11.6 bit

#### Spatial nonuniformities

DSNU<sub>1288</sub> 0.29 e<sup>-</sup>

0.12 DN

PRNU<sub>1288</sub> 0.35 %

#### Linearity error

LE<sub>min</sub> -0.44%

LE<sub>max</sub> 0.39%

#### Dark current

$\mu_{c,\text{mean}}$  0.9 ± 0.0 e<sup>-</sup>/s

0.38 DN/s

$\mu_{c,\text{var}}$  8.9 ± 5.0 e<sup>-</sup>/s

$T_d$  — °C