EMVA 1288 Data Sheet m0810

This datasheet describes the specification according to the standard 1288 release 3.1 for "Characterization and Presentation of Specification Data for Image Sensors and Cameras" issued on December 30, 2016 by the European Machine Vision Association (EMVA), published at `www.standard1288.org` and the *zenodo EMVA 1288 community* with proprietary extensions from AEON. The measurements were performed with the AEON ACC3 Release 6, 26.11.2016, SN 0005(MatrixVision.

Measurements performed by T.Renner, Matrix Vision GmbH

Vendor	Matrix Vision
Model	mvBlueFOX3-2071C
Serial number	FF003914
Sensor diagonal	17.55 mm
Lens category	C-Mount
Resolution	3216 × 2208, 12 bit
Pixel size (h×v)	4.50 μm × 4.50 μm
Sensor	IMX420
Sensor type	CMOS
Shutter type	Global
Overlap cap.	Overlapping
Max. frame rate	26.7 Hz
Interface type	USB3 Vision

Type of data presented	Single
Operation point 1 (page 5)	
Wavelength centroid	468.0 nm
Wavelength FWHM	20.0 nm
Gain, black-level	0dB, 0.1
Operation point 2 (page 20)	
Wavelength centroid	535.0 nm
Wavelength FWHM	31.0 nm
Gain, black-level	0dB, 0.1
Operation point 3 (page 35)	
Wavelength centroid	630.0 nm
Wavelength FWHM	13.0 nm
Gain, black-level	0dB, 0.1
Optional data measured	
None	



Summary Sheet for Operation Point 1 at a Wavelength of 468 nm

Type of data	Single	Gain, black-level	0dB, 0.1
Exposure control	By irradiance	Environmental temperature	22.2°C
Exposure time	18.00 ms	Camera body temperature	33.6°C
Frame rate	24.6 Hz	Internal temperature(s)	—
Data transfer mode	BayerRG12	Wavelength, centr., FWHM	468 nm, 20.0 nm

Photon Transfer



Signal-to-Noise Ratio



Quantum efficiency

η	50.5%

Overall system gain

K	0.161 DN/e$^-$
$1/K$	6.229 e$^-$/DN

Temporal dark noise

σ_d	5.51 e$^-$
$\sigma_{y.\mathrm{dark}}$	0.93 DN

Signal-to-noise ratio

$\mathrm{SNR}_{\max}$	158
	44.0 dB
	7.3 bit
$1/\mathrm{SNR}_{\max}$	0.63 %

Absolute sensitivity threshold

$\mu_{p.\min}$	12.52 p
$\mu_{p.\mathrm{min.area}}$	0.618 p/μm^2
$\mu_{e.\min}$	6.32 e$^-$
$\mu_{e.\mathrm{min.area}}$	0.312 e$^-$/μm^2

Saturation capacity

$\mu_{p.\mathrm{sat}}$	49404 p
$\mu_{p.\mathrm{sat.area}}$	2440 p/μm^2
$\mu_{e.\mathrm{sat}}$	24945 e$^-$
$\mu_{e.\mathrm{sat.area}}$	1232 e$^-$/μm^2

Dynamic range

DR	3947
	71.9 dB
	11.9 bit

Spatial nonuniformities

DSNU_{1288}	1.14 e$^-$
	0.18 DN
PRNU_{1288}	0.53 %

Linearity error

$\mathrm{LE}_{\min}$	-0.23%
$\mathrm{LE}_{\max}$	0.51%

Dark current

$\mu_{c.\mathrm{mean}}$	-18.4 ± 6.5 e$^-$/s
	-2.95 DN/s
$\mu_{c.\mathrm{var}}$	-1.5 ± 2.8 e$^-$/s
T_d	— °C

Summary Sheet for Operation Point 2 at a Wavelength of 535 nm

Type of data	Single	Gain, black-level	0dB, 0.1
Exposure control	By irradiance	Environmental temperature	22.4°C
Exposure time	18.00 ms	Camera body temperature	36.9°C
Frame rate	24.6 Hz	Internal temperature(s)	—
Data transfer mode	BayerRG12	Wavelength, centr., FWHM	535 nm, 31.0 nm

Photon Transfer



Signal-to-Noise Ratio



Quantum efficiency

η	61.3%

Overall system gain

K	0.161 DN/e$^-$
$1/K$	6.200 e$^-$/DN

Temporal dark noise

σ_d	5.51 e$^-$
$\sigma_{y.\mathrm{dark}}$	0.93 DN

Signal-to-noise ratio

$\mathrm{SNR}_{\max}$	157
	43.9 dB
	7.3 bit
$1/\mathrm{SNR}_{\max}$	0.64 %

Absolute sensitivity threshold

$\mu_{p.\mathrm{min}}$	10.30 p
$\mu_{p.\mathrm{min.area}}$	0.508 p/μm^2
$\mu_{e.\mathrm{min}}$	6.31 e$^-$
$\mu_{e.\mathrm{min.area}}$	0.312 e$^-$/μm^2

Saturation capacity

$\mu_{p.\mathrm{sat}}$	40203 p
$\mu_{p.\mathrm{sat.area}}$	1985 p/μm^2
$\mu_{e.\mathrm{sat}}$	24655 e$^-$
$\mu_{e.\mathrm{sat.area}}$	1218 e$^-$/μm^2

Dynamic range

DR	3905
	71.8 dB
	11.9 bit

Spatial nonuniformities

DSNU_{1288}	0.78 e$^-$
	0.13 DN
PRNU_{1288}	0.68 %

Linearity error

$\mathrm{LE}_{\min}$	-0.43%
$\mathrm{LE}_{\max}$	0.94%

Dark current

$\mu_{c.\mathrm{mean}}$	-18.3 ± 6.5 e$^-$/s
	-2.96 DN/s
$\mu_{c.\mathrm{var}}$	-1.5 ± 2.8 e$^-$/s
T_d	— °C

Summary Sheet for Operation Point 3 at a Wavelength of 630 nm

Type of data	Single	Gain, black-level	0dB, 0.1
Exposure control	By irradiance	Environmental temperature	22.6°C
Exposure time	18.00 ms	Camera body temperature	38.2°C
Frame rate	24.6 Hz	Internal temperature(s)	—
Data transfer mode	BayerRG12	Wavelength, centr., FWHM	630 nm, 13.0 nm

Photon Transfer



Signal-to-Noise Ratio



Quantum efficiency

η	55.6%

Overall system gain

K	0.160 DN/e$^-$
$1/K$	6.233 e$^-$/DN

Temporal dark noise

σ_d	5.55 e$^-$
$\sigma_{y.\mathrm{dark}}$	0.94 DN

Signal-to-noise ratio

$\mathrm{SNR}_{\max}$	158
	44.0 dB
	7.3 bit
$1/\mathrm{SNR}_{\max}$	0.63 %

Absolute sensitivity threshold

$\mu_{p.\min}$	11.42 p
$\mu_{p.\mathrm{min.area}}$	0.564 p/μm^2
$\mu_{e.\min}$	6.35 e$^-$
$\mu_{e.\mathrm{min.area}}$	0.314 e$^-$/μm^2

Saturation capacity

$\mu_{p.\mathrm{sat}}$	44726 p
$\mu_{p.\mathrm{sat.area}}$	2209 p/μm^2
$\mu_{e.\mathrm{sat}}$	24881 e$^-$
$\mu_{e.\mathrm{sat.area}}$	1229 e$^-$/μm^2

Dynamic range

DR	3917
	71.9 dB
	11.9 bit

Spatial nonuniformities

DSNU_{1288}	0.98 e$^-$
	0.16 DN
PRNU_{1288}	0.82 %

Linearity error

$\mathrm{LE}_{\min}$	-0.38%
$\mathrm{LE}_{\max}$	0.35%

Dark current

$\mu_{c.\mathrm{mean}}$	-18.3 ± 6.5 e$^-$/s
	-2.96 DN/s
$\mu_{c.\mathrm{var}}$	-1.8 ± 2.9 e$^-$/s
T_d	— °C