EMVA 1288 Data Sheet m0833

This datasheet describes the specification according to the standard 1288 release 3.1 for "Characterization and Presentation of Specification Data for Image Sensors and Cameras" issued on December 30, 2016 by the European Machine Vision Association (EMVA), published at `www.standard1288.org` and the *zenodo EMVA 1288 community* with proprietary extensions from AEON. The measurements were performed with the AEON ACC3 Release 6, 26.11.2016, SN 0005(MatrixVision.

Measurements performed by T.Renner, Matrix Vision GmbH

Vendor	Matrix Vision
Model	BF3-4-0169ZC
Serial number	FF005455
Sensor diagonal	21.66 mm
Lens category	C-Mount
Resolution	5472 × 3080, 12 bit
Pixel size (h×v)	3.45 μm × 3.45 μm
Sensor	IMX387
Sensor type	CMOS
Shutter type	Global
Overlap cap.	Overlapping
Max. frame rate	11.2 Hz
Interface type	USB3 Vision

Type of data presented	Single
Operation point 1 (page 5)	
Wavelength centroid	468.0 nm
Wavelength FWHM	20.0 nm
Gain, black-level	0dB, 0.1
Operation point 2 (page 20)	
Wavelength centroid	535.0 nm
Wavelength FWHM	31.0 nm
Gain, black-level	0dB, 0.1
Operation point 3 (page 35)	
Wavelength centroid	630.0 nm
Wavelength FWHM	13.0 nm
Gain, black-level	0dB, 0.1
Optional data measured	
None	



Summary Sheet for Operation Point 1 at a Wavelength of 468 nm

Type of data	Single	Gain, black-level	0dB, 0.1
Exposure control	By irradiance	Environmental temperature	$23.1°C$
Exposure time	18.00 ms	Camera body temperature	$33.5°C$
Frame rate	11.2 Hz	Internal temperature(s)	—
Data transfer mode	BayerRG12	Wavelength, centr., FWHM	468 nm, 20.0 nm

Photon Transfer



Signal-to-Noise Ratio



Quantum efficiency

η	43.2%

Overall system gain

K	0.381 DN/e$^-$
$1/K$	2.624 e$^-$/DN

Temporal dark noise

σ_d	2.32 e$^-$
$\sigma_{y.\mathrm{dark}}$	0.93 DN

Signal-to-noise ratio

$\mathrm{SNR}_{\max}$	102
	40.2 dB
	6.7 bit
$1/\mathrm{SNR}_{\max}$	0.98 %

Absolute sensitivity threshold

$\mu_{p.\mathrm{min}}$	6.93 p
$\mu_{p.\mathrm{min.area}}$	0.582 p/μm^2
$\mu_{e.\mathrm{min}}$	3.00 e$^-$
$\mu_{e.\mathrm{min.area}}$	0.252 e$^-$/μm^2

Saturation capacity

$\mu_{p.\mathrm{sat}}$	24069 p
$\mu_{p.\mathrm{sat.area}}$	2022 p/μm^2
$\mu_{e.\mathrm{sat}}$	10408 e$^-$
$\mu_{e.\mathrm{sat.area}}$	874 e$^-$/μm^2

Dynamic range

DR	3475
	70.8 dB
	11.8 bit

Spatial nonuniformities

DSNU_{1288}	1.02 e$^-$
	0.39 DN
PRNU_{1288}	0.69 %

Linearity error

$\mathrm{LE}_{\min}$	-0.70%
$\mathrm{LE}_{\max}$	1.19%

Dark current

$\mu_{c.\mathrm{mean}}$	-2.3 ± 2.4 e$^-$/s
	-0.89 DN/s
$\mu_{c.\mathrm{var}}$	1.4 ± 0.5 e$^-$/s
T_d	— °C

Summary Sheet for Operation Point 2 at a Wavelength of 535 nm

Type of data	Single	Gain, black-level	0dB, 0.1
Exposure control	By irradiance	Environmental temperature	23.2°C
Exposure time	18.00 ms	Camera body temperature	33.6°C
Frame rate	11.2 Hz	Internal temperature(s)	—
Data transfer mode	BayerRG12	Wavelength, centr., FWHM	535 nm, 31.0 nm

Photon Transfer



Signal-to-Noise Ratio



Quantum efficiency

η	55.9%

Overall system gain

K	0.381 DN/e$^-$
$1/K$	2.622 e$^-$/DN

Temporal dark noise

σ_d	2.32 e$^-$
$\sigma_{y.\mathrm{dark}}$	0.93 DN

Signal-to-noise ratio

$\mathrm{SNR}_{\mathrm{max}}$	102
	40.1 dB
	6.7 bit
$1/\mathrm{SNR}_{\mathrm{max}}$	0.98 %

Absolute sensitivity threshold

$\mu_{p.\mathrm{min}}$	5.36 p
$\mu_{p.\mathrm{min.area}}$	0.450 p/μm^2
$\mu_{e.\mathrm{min}}$	2.99 e$^-$
$\mu_{e.\mathrm{min.area}}$	0.251 e$^-$/μm^2

Saturation capacity

$\mu_{p.\mathrm{sat}}$	18457 p
$\mu_{p.\mathrm{sat.area}}$	1551 p/μm^2
$\mu_{e.\mathrm{sat}}$	10311 e$^-$
$\mu_{e.\mathrm{sat.area}}$	866 e$^-$/μm^2

Dynamic range

DR	3445
	70.7 dB
	11.8 bit

Spatial nonuniformities

DSNU_{1288}	0.99 e$^-$
	0.38 DN
PRNU_{1288}	0.75 %

Linearity error

$\mathrm{LE}_{\mathrm{min}}$	-1.03%
$\mathrm{LE}_{\mathrm{max}}$	1.68%

Dark current

$\mu_{c.\mathrm{mean}}$	-2.4 ± 2.4 e$^-$/s
	-0.91 DN/s
$\mu_{c.\mathrm{var}}$	1.3 ± 0.5 e$^-$/s
T_{d}	— °C

Summary Sheet for Operation Point 3 at a Wavelength of 630 nm

Type of data	Single	Gain, black-level	0dB, 0.1
Exposure control	By irradiance	Environmental temperature	23.3°C
Exposure time	18.00 ms	Camera body temperature	33.7°C
Frame rate	11.2 Hz	Internal temperature(s)	—
Data transfer mode	BayerRG12	Wavelength, centr., FWHM	630 nm, 13.0 nm

Photon Transfer



Signal-to-Noise Ratio



Quantum efficiency

η	48.0%

Overall system gain

K	0.381 DN/e$^-$
$1/K$	2.623 e$^-$/DN

Temporal dark noise

σ_d	2.32 e$^-$
$\sigma_{y.\mathrm{dark}}$	0.93 DN

Signal-to-noise ratio

$\mathrm{SNR}_{\mathrm{max}}$	102
	40.2 dB
	6.7 bit
$1/\mathrm{SNR}_{\mathrm{max}}$	0.98 %

Absolute sensitivity threshold

$\mu_{p.\mathrm{min}}$	6.23 p
$\mu_{p.\mathrm{min.area}}$	0.523 p/μm^2
$\mu_{e.\mathrm{min}}$	2.99 e$^-$
$\mu_{e.\mathrm{min.area}}$	0.251 e$^-$/μm^2

Saturation capacity

$\mu_{p.\mathrm{sat}}$	21662 p
$\mu_{p.\mathrm{sat.area}}$	1820 p/μm^2
$\mu_{e.\mathrm{sat}}$	10405 e$^-$
$\mu_{e.\mathrm{sat.area}}$	874 e$^-$/μm^2

Dynamic range

DR	3479
	70.8 dB
	11.8 bit

Spatial nonuniformities

DSNU_{1288}	0.99 e$^-$
	0.38 DN
PRNU_{1288}	0.97 %

Linearity error

$\mathrm{LE}_{\mathrm{min}}$	-0.71%
$\mathrm{LE}_{\mathrm{max}}$	0.31%

Dark current

$\mu_{c.\mathrm{mean}}$	-2.8 ± 2.5 e$^-$/s
	-1.07 DN/s
$\mu_{c.\mathrm{var}}$	1.9 ± 0.1 e$^-$/s
T_{d}	— °C