EMVA 1288 Data Sheet m0794

This datasheet describes the specification according to the standard 1288 release 3.1 for "Characterization and Presentation of Specification Data for Image Sensors and Cameras" issued on December 30, 2016 by the European Machine Vision Association (EMVA), published at `www.standard1288.org` and the *zenodo EMVA 1288 community* with proprietary extensions from AEON. The measurements were performed with the AEON ACC3 Release 6, 26.11.2016, SN 0005(MatrixVision.

Measurements performed by T.Renner, Matrix Vision GmbH

Vendor	MATRIX VISION
Model	BF3-4-0315ZG
Serial number	FF003428
Sensor diagonal	27.94 mm
Lens category	M42
Resolution	6480 × 4856, 12 bit
Pixel size (h×v)	3.45 μm × 3.45 μm
Sensor	IMX342
Sensor type	CMOS
Shutter type	Global
Overlap cap.	Overlapping
Max. frame rate	6.0 Hz
Interface type	USB3 Vision

Type of data presented	Single
Operation point 1 (page 3)	
Wavelength centroid	536.0 nm
Wavelength FWHM	31.0 nm
Gain, black-level	0dB, 0.1
Optional data measured	
None	



Summary Sheet for Operation Point 1 at a Wavelength of 536 nm

Type of data	Single	Gain, black-level	0dB, 0.1
Exposure control	By irradiance	Environmental temperature	25.5°C
Exposure time	18.00 ms	Camera body temperature	35.4°C
Frame rate	5.5 Hz	Internal temperature(s)	—
Data transfer mode	Mono12	Wavelength, centr., FWHM	536 nm, 31.0 nm

Photon Transfer



Signal-to-Noise Ratio



Quantum efficiency

η	64.0%

Overall system gain

K	0.379 DN/e$^-$
$1/K$	2.640 e$^-$/DN

Temporal dark noise

σ_d	2.32 e$^-$
$\sigma_{y.\mathrm{dark}}$	0.92 DN

Signal-to-noise ratio

$\mathrm{SNR}_{\max}$	96
	39.7 dB
	6.6 bit
$1/\mathrm{SNR}_{\max}$	1.04 %

Absolute sensitivity threshold

$\mu_{p.\mathrm{min}}$	4.67 p
$\mu_{p.\mathrm{min.area}}$	0.393 p/μm^2
$\mu_{e.\mathrm{min}}$	2.99 e$^-$
$\mu_{e.\mathrm{min.area}}$	0.251 e$^-$/μm^2

Saturation capacity

$\mu_{p.\mathrm{sat}}$	14439 p
$\mu_{p.\mathrm{sat.area}}$	1213 p/μm^2
$\mu_{e.\mathrm{sat}}$	9237 e$^-$
$\mu_{e.\mathrm{sat.area}}$	776 e$^-$/μm^2

Dynamic range

DR	3090
	69.8 dB
	11.6 bit

Spatial nonuniformities

DSNU_{1288}	0.90 e$^-$
	0.34 DN
PRNU_{1288}	1.12 %

Linearity error

$\mathrm{LE}_{\min}$	-0.61%
$\mathrm{LE}_{\max}$	0.77%

Dark current

$\mu_{c.\mathrm{mean}}$	-8.4 ± 2.8 e$^-$/s
	-3.18 DN/s
$\mu_{c.\mathrm{var}}$	1.7 ± 0.4 e$^-$/s
T_d	— °C