





Kenndaten

Werkstoff	Edelstahl 1.4541
Betriebstemperatur	-20°C...+120°C (nur Schwimmer)
Druck (stat.)	max 15 bar
WIG - geschweißt	
Abmessungen	siehe oben
Gewicht	69g
Einbaulage	Paraboloid nach unten
min. Flüssigkeitsdichte	0.6g/ccm

*)

Bei Montage oder Demontage des Splints darf die Schweißnaht am Ende des Schutzrohrs nicht mechanisch belastet werden. Den Splint durch die Bohrung führen und mit einer Zange an der Öse halten. Mit einer zweiten Zange nacheinander die geraden Enden des Splints um das Rohr biegen. Achtung: Splint nur einmal verwendbar !!

Werte wenn nicht anders angegeben unter Nennbedingungen



Technical Data

Material	Stainless Steel 1.4541
Operating temperature	-20°C...+120°C (float only)
Pressure (static)	max 15 bar
Float TIG welded	
Dimensions	see above
Weight	69g
Orientation	Parabola towards bottom
Min. specific gravity	0.6g/ccm

*)

When assembling or disassembling the cotter pin, there is no load permitted on the weld bead at the end of the pressure tube. Feed the cotter pin through the hole and use pliers to hold at the eye. Use a second pliers to bend the ends of the pin around the tube.
Caution: Cotter pin may be used only once !!

Technical data according to normal conditions