

BALLUFF

Balluff BVS HS-QC
Handheld Barcode Reader



Quick Guide



english

World Headquarters Germany

Balluff GmbH
Schurwaldstraße 9
73765 Neuhausen a.d.F
Service-Hotline +49 7158 173-370
service@balluff.de

Subsidiaries

USA

Balluff Inc.
8125 Holton Drive
Florence,
Kentucky 41042-0937
Phone (859) 727-2200,
1-800-543-8390
applications@balluff.com

Produced by DATALOGIC S.r.l.

Copyright Notice

Copyright © Balluff GmbH, Neuhausen a.d.F., Germany, 2015. All rights reserved. In particular: Reproduction, modification, dissemination and translation into other languages.

Please note that all texts, graphics and images in this operating manual are subject to copyright and other protection laws. Commercial copies, reproductions, modifications and dissemination in any form require prior written agreement from Balluff GmbH.

Owners of Balluff products are hereby granted a non-exclusive, revocable license to reproduce and transmit this documentation for the purchaser's own internal business purposes. Purchaser shall not remove or alter any proprietary notices, including copyright notices, contained in this documentation and shall ensure that all notices appear on any reproductions of the documentation.

An electronic version of this document is downloadable from the Balluff website (www.Balluff.com).

If you visit our website and would like to make comments or suggestions about this or other Balluff publications, please let us know via the "Contact" page.

Disclaimer

This document contains operating instructions and technical documentation for BVS HS Handscanners by Balluff GmbH. All specifications and instructions in this document, especially the Safety Notes section, must be strictly observed. This operator's manual must be carefully stored so that it is always available. The information and illustrations in this operating manual were carefully checked to the best of our ability. Nevertheless, Balluff GmbH cannot assume any liability for the correctness and completeness of this information, since in spite of all due care errors and mistakes cannot be completely avoided. In particular this information and the illustrations do not constitute agreements as to condition according to § 434 of the German Civil Code or guarantees according to § 443 of the GCC.

The information in this manual is based on current knowledge and experience of Balluff GmbH.

No legally binding assurance of certain properties or suitability for a specific purpose can be derived from the information in this operating manual.

Trademarks

The product, goods, company and technology names are trademarks of the respective companies. In particular: Microsoft®, Windows®, Windows XP®, .NET FRAMEWORK ® and Windows 7® are registered trademarks of Microsoft Corporation ; QR Code (R) is a registered trademark of Denso Wave Incorporated. Balluff and Balluff Logo are registered trademarks of Balluff GmbH in many countries. It is the user's responsibility to observe any property rights and provisions.

Patents

This product is covered by one or more of the following patents:

Design patents: EP002158717, ZL201330271434.1

Utility patents: EP0996284B1, EP0997760B1, EP0999514B1, EP1128315B1, EP1396811B1, EP1413971B1, EP1828957B1, JP4435343B2, US6478224, US6512218, US6513714, US6561427, US6808114, US6997385, US7053954, US7075663, US7234641, US7387246, US7721966, US8245926, US8561906

All patents belong to a third party!

BVS HS-QC
Handheld Barcode Reader

END USER SOFTWARE LICENSE AGREEMENT (EULA)	4
Description	8
Setting Up the Reader	9
Connect/Disconnect Cable to Reader	9
Using the Balluff BVS HS-Q reader	10
Selecting the Interface Type	11
Interface Selection	11
Configuring the Interface	12
Keyboard Interface	13
Scancode Tables	14
Country Mode	14
Programming	18
Using Programming Barcodes	18
Configure Other Settings	18
Resetting Product Defaults	18
Caps Lock State	19
Numlock	20
Reading Parameters	21
Aiming System	21
Good Read Green Spot Duration	21
Operating Modes	22
Scan Mode	22
Pick Mode	24
Multiple Label Reading	24
Technical Specifications	25
LED and Beeper Indications	29
Error Codes	31
Cleaning	32
Regulatory Addendum	33
Regulatory Information	35
Power Supply	36
Imager Labeling	37
WEEE Statement	38
DECLARATION OF CONFORMITY	40
Ergonomic Recommendations	41
Services and Support	41

BALLUFF GMBH

1 END USER SOFTWARE LICENSE AGREEMENT (EULA) FOR THE BVS HS-Q Series

Notice to End User: There are two types of software covered by this END USER LICENSE AGREEMENT ("EULA"): (1) The Balluff Product you have acquired contains embedded software ("Embedded Software") which is integral to the Product's operation; and (2) Optional Application Software provided to you on an optional basis ("Application Software"). Embedded Software and Application Software are collectively referred to as "Software" and are subject to the terms and conditions contained in this EULA. Software is provided only for use with, and for authorized end users of, the Balluff BVS HS-Q Series of hand held readers ("Product"). Portions of the Embedded Software include or operate with Open Source software or libraries ("Open Source"). Use of Open Source is subject to the Open Source licenses entitled "*****_**_BVS_HS-QReaders_OpenSource.zip" available at the following website <http://www.balluff.com>.

This EULA (End User Software License Agreement) ("EULA" or "Agreement") is a legally binding agreement governing the licensing of the Software and Documentation by Balluff GbmH. and its subsidiaries and affiliates ("Balluff") to the entity or person who has purchased or otherwise acquired a Balluff Product ("End User"). For purposes of this Agreement, any software that is not Embedded Software or Application Software is software associated with a separate end-user license agreement is licensed to you under the terms of that license agreement. Balluff and End User hereby agree as follows:

1. Definitions.

- 1.1 "Affiliate" means a business entity currently existing or later acquired that is controlled by, or is under common control with Balluff GmbH.
- 1.2 "Documentation" means materials such as user's guides, program reference guides, quick reference guides, manuals, or similar materials associated with or related to the Balluff Product, whether in printed, "online", or other form.
- 1.3 "Proprietary Information" means: (a) source code, object code, software, documentation, and any related internal design, system design, data base design, algorithms, technology, technical data or information, implementation techniques, and trade secrets related to the Software, (b) any other trade secrets marked appropriately or identified as proprietary or confidential, and (c) any information that End User, under the circumstances, should recognize as confidential. Proprietary Information does not include any information that the receiving party can establish was (1) in the public domain, (2) already in the receiving party's possession or rightfully known prior to receipt, (3) rightfully learned from a third party not in violation of any other's proprietary rights, or (4) independently developed without access to Proprietary Information.
- 1.4 "Balluff Product" means the Balluff BVS HS-Q series scanner product, including all embedded Software in and all Documentation related to such product, which has been purchased or otherwise acquired by End User, whether obtained directly or indirectly from Balluff.
- 1.5 "Software" means any software or computer programs of Balluff or its third party licensors in machine readable form which is embedded in the Balluff Product, whether obtained directly or indirectly from Balluff, including any replacement, update, upgrade, enhancement or modification.

2. Scope Of License Granted.

- 2.1 Balluff grants to End User a non-exclusive, non-transferable, perpetual license to use the Software, solely on the Balluff Product in which it is embedded ("designated Balluff Product"), in machine-readable form only, solely for End User's internal business purposes. This Agreement does not convey ownership of the Software to End User. Title to the Software shall be and remain with Balluff or the third party from whom Balluff has obtained a licensed right. As used in this Agreement, the term "purchase" or its equivalents when applied to the Software shall mean "acquire under license". End User is not entitled to receipt or use of the source code to any Software.
- 2.2 End User shall not copy, modify, decompile, disassemble, reverse engineer, or otherwise reproduce or remanufacture the Software, whether modified or unmodified, nor sell, assign, sublicense, distribute, lend, rent, give, or otherwise transfer the Software to any other person or organization, for purposes other than as expressly provided in this Agreement, without Balluff's prior written consent.

1

END USER SOFTWARE LICENSE AGREEMENT (EULA)

3. Transfers, Support.

- 3.1 Any copying, installing, reproduction, remanufacture, reverse engineering, electronic transfer, or other use of the Software on other than the designated Balluff Product will be a material breach of this Agreement. However, Balluff may elect not to terminate this Agreement or the granted licenses, but instead may elect to notify End User that End User is deemed to have ordered and accepted a license for each breaching use. End User shall pay Balluff the applicable list price for such licenses as of the date of such breach.
- 3.2 End User may obtain support for Software from Balluff at Balluff's standard support fees and under Balluff's standard support terms and conditions in effect at the time the support is requested.
- 3.3 End User shall make at its own cost and liability a back up copy of any data processed and/or run through the Software

4. Intellectual Property.

End User acknowledges that the Software constitutes valuable trade secrets of Balluff or Balluff's third party licensors and that the Software is protected by intellectual property laws and treaties. The license set forth in this Agreement does not transfer to End User any ownership of Balluff's or its third party licensors' copyrights, patents, trademarks, service marks, trade secrets, or other intellectual property rights and End User shall have no right to commence any legal actions to obtain such rights. End User shall not remove, modify, or take any other action that would obscure any copyright, trademark, patent marking, or other intellectual property notices contained in or on the Balluff Product.

5. Proprietary Information.

- 5.1 End User acknowledges that Proprietary Information is the confidential, proprietary, and trade secret property of Balluff and Balluff's third party licensors and End User acquires no right or interest in any Proprietary Information.
- 5.2 End User shall not disclose, provide, or otherwise make available the Proprietary Information of Balluff or its third party licensors to any person other than End User's authorized employees or agents who are under confidentiality agreement, and End User shall not use the Proprietary Information other than in conjunction with use of the Balluff Product exclusively for End User's internal business purposes. End User shall take steps to protect the Proprietary Information no less securely than if it were End User's own intellectual property.
- 5.3 The provisions of this Proprietary Information Section shall survive and continue for five (5) years after the termination of this Agreement.

6. Limited Warranty.

- 6.1 Balluff warrants that, under normal use and operation, the Balluff Product will conform substantially to the applicable Documentation for the period specified in the Documentation. During this period, for all reproducible non-conformities for which Balluff has been given written notice, Balluff will use commercially reasonable efforts to remedy nonconformities verified by Balluff. End User agrees to supply Balluff with all reasonably requested information and assistance necessary to help Balluff in remedying such nonconformities. For all defects reported to Balluff within the warranty period, Balluff's liability is limited to providing End User with one copy of corrections or responding to End User's problem reports according to Balluff's standard assistance practices. Balluff does not warrant that the product will meet End User's requirements or that use of the product will be uninterrupted or error free, or that Balluff's remedial efforts will correct any nonconformance. This limited warranty does not cover any product that has been subjected to damage or abuse, whether intentionally, accidentally, or by neglect, or to unauthorized repair or unauthorized installation, and shall be void if End User modifies the product, uses the product in any manner other than as established in the Documentation, or if End User breaches any of the provisions of this Agreement.
- 6.2 EXCEPT AS PROVIDED IN THIS AGREEMENT, THE BALLUFF PRODUCT IS PROVIDED "AS IS" AND BALLUFF MAKES NO WARRANTIES OF ANY KIND, EXPRESS OR IMPLIED, WRITTEN OR ORAL, WITH RESPECT TO THE PRODUCT, AND SPECIFICALLY DISCLAIMS THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE.

7. Infringement.

- 7.1 Balluff will defend End User against any claim in a lawsuit that the Balluff Product furnished hereunder infringe a United States patent or copyright of a third party and Balluff will pay any damages finally awarded against End User by a court of competent jurisdiction that are attributable to such claim or will pay End User's part of any settlement that is attributable to such claim, provided, that 1) End User notifies Balluff promptly in writing of the claim, 2) Balluff controls the defense or settlement of the claim, and 3) End User cooperates fully with Balluff in such defense or settlement. All notices of a claim should be sent to Balluff GmbH Schurwaldstraße 9, D-73765 Neuhausen/Fildern, Germany. In the defense or settlement of any such claim, Balluff may, at its option, 1) procure for End User the right to continue using the Balluff Product, 2) modify the Balluff Product so that it becomes non-infringing, 3) replace the Balluff Product with an equivalent product not subject to such claim, or 4) provide End User an opportunity to return the Balluff Product and receive a refund of the purchase price paid, less a reasonable allowance for use.
- 7.2 Balluff shall have no liability to End User for claims of infringement based upon 1) the use of any Balluff Product in combination with any product which Balluff has not either furnished or authorized for use with Product 2) the use of any Balluff Product designed, manufactured, or modified to the specifications of End User, or 3) End User's modification of the Balluff Product without written authorization from Balluff.
- 7.3 THE FOREGOING STATES BALLUFF'S COMPLETE AND ENTIRE OBLIGATION CONCERNING CLAIMS OF PATENT, COPYRIGHT, OR OTHER INTELLECTUAL PROPERTY INFRINGEMENT, CANCELS AND SUPERCEDES ANY PRIOR AGREEMENTS, WHETHER ORAL OR WRITTEN, BETWEEN THE PARTIES CONCERNING SUCH CLAIMS, AND WILL NOT BE MODIFIED OR AMENDED BY ANY PAST, CONTEMPORANEOUS, OR FUTURE AGREEMENTS OR DEALINGS BETWEEN THE PARTIES, WHETHER ORAL OR WRITTEN, EXCEPT AS SET FORTH IN A FUTURE WRITING SIGNED BY BOTH PARTIES

8. Limitation Of Liability.

IN NO EVENT SHALL BALLUFF'S LIABILITY FOR DAMAGES, IF ANY, WHETHER BASED UPON CONTRACT, TORT (INCLUDING NEGLIGENCE), PRODUCT LIABILITY, STRICT LIABILITY, WARRANTY, OR ANY OTHER BASIS, WILL INCLUDE LOST PROFITS, LOST DATA, INTERRUPTION OF BUSINESS OR SERVICE, OR FOR ANY OTHER SPECIAL, PUNITIVE, EXEMPLARY, OR OTHER SIMILAR DAMAGES, EVEN IF BALLUFF HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES. BALLUFF SHALL BE LIABLE FOR THOSE DAMAGES WHICH OCCURRED DIRECTLY FROM ANY BREACH OF CONSTITUTIONAL OBLIGATIONS OF THIS AGREEMENT AND WHICH HAVE CAUSED ACTUAL FINANCIAL LOSS AS OF THEIR OCCURRENCE.

9. Government Restricted Rights; International Use.

- 9.1 Use, duplication, or disclosure of the Software by the U.S. Government is subject to the restrictions for computer software developed at private expense as set forth in the U.S. Federal Acquisition Regulations at FAR 52.227-14(g), or 52.227-19 or in the Rights in Technical Data and Computer Software clause at DFARS 252.227-7013(c)(1)(ii), whichever is applicable.
- 9.2 End User must comply with the applicable local laws of the country in which the Balluff Product is used, with U.S. export control laws, and with this Agreement. The provisions of the "United Nations Convention on International Sale of Goods" shall not apply to this Agreement.

10. Termination.

- 10.1 Either party may terminate this Agreement or any license granted under this Agreement at any time upon written notice if the other party breaches any provision of this Agreement.
- 10.2 Upon termination of this Agreement, End User immediately shall cease using any nonembedded software and shall return to Balluff or destroy all non-embedded software covered by this Agreement, and shall furnish Balluff with a certificate of compliance with this provision signed by an officer or authorized representative of End User. For embedded software, End User agrees to sign a waiver prepared by Balluff concerning further use of the embedded Software. End User's resumed or continued use of the embedded Software after termination shall constitute End User's agreement to be bound by the terms and conditions of this Agreement for such use.

11. General Provisions.

- 11.1 Entire Agreement; Amendment. This document contains the entire agreement between the parties relating to the licensing of the Software and supersedes all prior or contemporaneous agreements, written or oral, between the parties concerning the licensing of the Software. This Agreement may not be changed, amended, or modified except by written document signed by Balluff.
- 11.2 Notice. All notices required or authorized under this Agreement shall be given in writing, and shall be effective when received, with evidence of receipt. Notices to Balluff shall be sent to the attention of Contract Administration, Balluff GmbH Schurwaldstraße 9, D-73765 Neuhausen/Fildern, Germany, or such other address as may be specified by Balluff in writing.
- 11.3 Waiver. A party's failure to enforce any of the terms and conditions of this Agreement shall not prevent the party's later enforcement of such terms and conditions.
- 11.4 It is agreed that (a) place of jurisdiction for legal actions falling within the jurisdiction as regards the subject matter of the Amtsgericht (local courts) shall be the Amtsgericht Stuttgart, Germany and (b) place of jurisdiction for legal actions falling within the jurisdiction as regards the subject matter of the Landgericht (regional courts) shall be the Landgericht Stuttgart, Germany.
- 11.5 German law shall apply exclusively without giving effect to its conflict of laws principles.
- 11.6 In addition to these EULA, the General Terms and Conditions of Balluff shall apply. In the event that individual provisions of the EULA contradict any provision of General Terms and Conditions, then, the EULA shall prevail. Without prejudice of the foregoing, should a clause of the EULA contradict the applicable law, then, to the extent the General Terms and Conditions have most favorable provision for Balluff in this respect, then the Parties shall refer to the General Terms and Conditions of Balluff.

- END -

Software Product Policy

Balluff reserves the right to ship its products with the latest version of software/firmware available. This provides our customers with the very latest in Balluff software technology.

2

Description

2 Description

The Balluff BVS HS-QC handheld barcode reader has been specifically created to meet the market demand for omni-directional reading performance on virtually all codes at an affordable price. Elegant design details are incorporated into a smaller, balanced lightweight enclosure without sacrificing durability.

Ideally suited for applications at the receiving/dispatching of goods departments this handheld reader features a new illumination and aiming system developed with the unique intent to reduce visual stress of the operator during the daily reading activities. It consists of a soft, dark red illumination combined with two blue LED triangles pointing at the targeted barcode. The result is a precise aiming system which contributes to low eye fatigue, yet still allows top operator efficiency.

Constructed with a combination of design and performance-based ideals such as barcode reading snappiness, motion tolerance, perfect ergonomics and an attractive price, this 2D imager is the ideal solution for the customer who is looking to replace their linear only reading readers with image-based technology.

Omni-Directional Operating	To read a symbol simply aim the reader and pull the trigger. The BVS HS-Q reader is a powerful omni-directional reader, so the orientation of the symbol is not important. The 'Green Spot' for good-read feedback helps to improve productivity in noisy environments or in situations where silence is required. When using the product with the cradle at a 45° position, the aiming pattern can work as an aiming system to aid in positioning the barcode for quick and intuitive reading.
Decoding	Reliably decodes all standard 1D (linear) and 2D barcodes, including GS1 DataBar™ linear codes, Postal Codes (China Post), Stacked Codes (such as GS1 DataBar Expanded Stacked, GS1 DataBar Stacked, GS1 DataBar, Stacked Omnidirectional). The data stream — acquired from decoding a symbol — is rapidly sent to the host. The reader is immediately available to read another symbol.

3 Setting Up the Reader


3 Setting Up the Reader

Follow the steps below to connect and get your reader up and communicating with its host.

- 1 Connect the Cable to the reader and the Host.
- 2 Configure the Interface (see page 12).
- 3 Configure the Reader starting on page 18 (optional, depends on settings needed).


3.1 Connect/Disconnect Cable to Reader

Figure 1: Connecting to the Reader



Host Connection — The BVS HS-QC plugs directly into the host device as shown in Figure 2. The power can also be supplied through an external power supply via the Interface Cable supplied with a power jack.

Figure 2: Connecting to the Host




4

Using the Balluff BVS HS-Q reader


4 Using the Balluff BVS HS-Q reader

The Balluff BVS HS-Q reader normally functions by capturing and decoding codes. The aiming system is activated on trigger pull and indicates the center of the field of view which should be positioned over the barcode:


Aiming System



Relative Size and Location of Aiming System Pattern



Linear barcode



2D Matrix symbol

A beam illuminates the label. The projected pattern of the aiming system will be smaller when the reader is closer to the barcode and larger when it is farther from the code. Symbologies with smaller bars or elements (mil size) should be read closer to the unit. Symbologies with larger bars or elements (mil size) should be read farther from the unit. If the aiming system is centered you will get a good read. Successful reading is signaled by an audible tone plus a good-read green spot LED indicator which is backprojected at the read code.

Reference the Balluff BVS HS-Q reader operation manual (OPM) on the Balluff website for more information about this feature and other programmable settings.

5

Selecting the Interface Type

5 Selecting the Interface Type

Upon completing the physical connection between the reader and its host, proceed directly to Interface Selection below for information and programming for the interface type the reader is connected to (for example: RS-232, Keyboard Wedge, USB, etc.) and scan the appropriate barcode to select your system's correct interface type.

5.1 Interface Selection

The reader model will support one of the following sets of host interfaces:

RS-232, USB

Information and programming options for each interface type are provided in this section. For defaults and additional information associated with each interface, proceed to the corresponding chapter in the operation manual.

5 Selecting the Interface Type

5.1.1 Configuring the Interface

Scan the appropriate programming barcode to select the interface type for your system.



NOTE

Unlike some other programming features and options, interface selections require that you scan only one programming barcode label. DO NOT scan an ENTER/EXIT barcode prior to scanning an interface selection barcode.

Some interfaces require the reader to start in the disabled state when powered up. If additional reader configuration is desired while in this state, pull the trigger and hold for 5 seconds. The reader will change to a state that allows programming with barcodes.

RS-232

RS-232 standard interface



Select RS232-STD

RS-232 Wincor-Nixdorf



Select RS232-WN

USB Com to simulate RS-232 standard interface



Select USB-COM-STD^a

5

Selecting the Interface Type

USB-OEM

USB-OEM



Select USB-OEM

a. Download the correct USB Com driver from www.balluff.com

5.1.2 Keyboard Interface

Use the programming barcodes to select options for USB Keyboard.

KEYBOARD

USB Keyboard with alternate key encoding



Select USB Alternate Keyboard

USB Keyboard for Apple computers



Select USB-KBD-APPLE

USB Keyboard with standard key encoding



Select USB Keyboard

5 Selecting the Interface Type

5.1.3 Scancode Tables

Reference the operation manual for information about control character emulation for keyboard interfaces.

5.1.4 Country Mode

This feature specifies the country/language supported by the keyboard. Only these interfaces support ALL Country Modes:

- USB Keyboard (without alternate key encoding)

All other interfaces support ONLY the following Country Modes: U.S., Belgium, Britain, France, Germany, Italy, Spain, Sweden.

COUNTRY MODE
 ENTER/EXIT PROGRAMMING MODE
 Country Mode = U.S.
 Country Mode = Belgium
 Country Mode = Croatia*
 Country Mode = Czech Republic*

5

Selecting the Interface Type

COUNTRY MODE (continued)



Country Mode = Denmark*



Country Mode = France



Country Mode = French Canadian*



Country Mode = Germany



Country Mode = Hungary*



Country Mode = Italy

*Supports only the interfaces listed in the Country Mode feature description

5

Selecting the Interface Type

COUNTRY MODE (continued)



Country Mode = Japanese 106-key*



Country Mode = Lithuanian*



Country Mode = Norway*



Country Mode = Poland*



Country Mode = Portugal*



Country Mode = Romania*

*Supports only the interfaces listed in the Country Mode feature description

5

Selecting the Interface Type

COUNTRY MODE (continued)



Country Mode = Spain



Country Mode = Sweden



Country Mode = Slovakia*



Country Mode = Switzerland*

*Supports only the interfaces listed in the Country Mode feature description

6 Programming

6 Programming

The reader is factory-configured with a set of standard default features. After scanning the interface barcode from the Interfaces section, select other options and customize your reader through use of the programming barcodes available in the operation manual. Check the corresponding features section for your interface, and also the Data Editing and Symbologies chapters of the OPM.

6.1 Using Programming Barcodes

This manual contains barcodes which allow you to reconfigure your reader. Some programming barcode labels, like the , require only the scan of that single label to enact the change.

Other barcodes require the reader to be placed in Programming Mode prior to scanning them. Scan an ENTER/EXIT barcode once to enter Programming Mode; scan the desired parameter settings; scan the ENTER/EXIT barcode again to accept your changes, which exits Programming Mode and returns the reader to normal operation.

6.2 Configure Other Settings

Additional programming barcodes are available in the OPM to allow for customizing programming features. If your installation requires different programming than the standard factory default settings, refer to the OPM.

6.3 Resetting Product Defaults

If you aren't sure what programming options are in your reader, or you've changed some options and want your custom factory settings restored, scan the barcode below to reset the reader to its initial configuration. Reference the OPM for other options, and a listing of standard factory settings.



NOTE

Factory defaults are based on the interface type. Be sure your reader is configured for the correct interface before scanning this label. See 5 for more information.



Reset Default Settings

6

Programming

6.3.1 Caps Lock State

This option specifies the format in which the reader sends character data. This applies to keyboard wedge interfaces. This does not apply when an alternate key encoding keyboard is selected.

CAPS LOCK STATE



ENTER/EXIT PROGRAMMING MODE



Caps Lock State = Caps Lock OFF



Caps Lock State = Caps Lock ON



Caps Lock State = AUTO Caps Lock Enable

6

Programming

6.3.2 Numlock

This option specifies the setting of the Numbers Lock (Numlock) key while in keyboard wedge interface. This only applies to alternate key encoding interfaces. It does not apply to USB keyboard.

NUMLOCK
 ENTER/EXIT PROGRAMMING MODE
 Numlock = Numlock key unchanged
 Numlock = Numlock key toggled

7 Reading Parameters

7 Reading Parameters

Move the reader toward the target and center the aiming pattern and illumination system to capture and decode the image. See ["Using the Balluff BVS HS-Q reader" on page 10](#) for more information.

The aiming system will briefly switch off after the acquisition time, and if no code is decoded will switch on again before the next acquisition. The illuminator will remain on until the symbol is decoded.

As you read code symbols, adjust the distance at which you are holding the reader.

7.1 Aiming System

A number of options for customizing control of the Aiming System are available. See the operation manual for more information and programming barcodes.

7.2 Good Read Green Spot Duration

Successful reading can be signaled by a good read green spot. Use the barcodes that follow to specify the duration of the good read pointer beam after a good read.

GOOD READ GREEN SPOT DURATION	
 ENTER/EXIT PROGRAMMING MODE	
 Disabled	 ◆ Short (300 ms)
 Medium (500 ms)	 Long (800 ms)

8 Operating Modes

8.1 Scan Mode

The imager can be set to operate in one of several scanning modes. See the OPM for more information and settings for any of the options:

Trigger Single (Default) — This mode is associated with typical handheld reader operation. When the trigger is pulled, illumination is turned on and the reader attempts to read a label. Scanning is activated until one of the following occurs:

- the programmable “maximum scan on time”¹ has elapsed
- a label has been read
- the trigger is released

Trigger Pulse Multiple — Scanning begins when the trigger is pulled and continues after the trigger is released, until the trigger is pulled again or until the programmable “maximum scan on time”¹ has elapsed. Reading a label does not disable scanning. Double Read Timeout¹ prevents undesired multiple reads while in this mode.

Trigger Hold Multiple — When the trigger is pulled, scanning starts and the product scans until the trigger is released or “maximum scan on time”¹ has elapsed. Reading a label does not disable scanning. Double Read Timeout¹ prevents undesired multiple reads while in this mode.

Always On — The illuminator is always ON and the reader is always ready for code reading. Double Read Timeout¹ prevents undesired multiple reads.

Flashing — The reader illuminator flashes on and off regardless of the trigger status. Code reading takes place only during the Flash On² time. Double Read Timeout¹ prevents undesired multiple reads.

Object Detection — The reader looks for changes within its field-of-view. The Aiming Pattern is always on to show the optimum reading area. If a predefined amount of movement is detected, the red illumination switches on. Scanning continues until a label is read or “maximum scan on time” is reached.

1. See the operational manual (OPM) for these and other programmable features
2. Controlled by Flash On Time and Flash Off Time. Use the OPM to program these options.

8 Operating Modes

SCAN MODE



◆ Scan Mode = Trigger Single



Scan Mode = Trigger Pulse
Multiple



Scan Mode = Trigger Hold
Multiple



Scan Mode = Flashing



Scan Mode = Always On



Scan Mode =
Object Detection

8 Operating Modes

8.2 Pick Mode

Specifies the ability of the reader to decode labels only when they are close to the center of the aiming pattern, which is the area indicated by the two blue arrows. Pick Mode is a Decoding and Transmission process where barcodes that are not within the configurable distance from the center of the aiming pattern are not acknowledged or transmitted to the host. It is active only while the reader is in Trigger Single mode. If the reader switches to a different Read Mode, Pick Mode is automatically disabled.



This feature is not compatible with Multiple Labels Reading in a Volume. See the OPM for more information.

NOTE

PICK MODE
 ENTER/EXIT PROGRAMMING MODE
 ◆ Pick Mode = Disable
 Pick Mode = Enable

8.3 Multiple Label Reading

The reader offers a number of options for multiple label reading. See the OPM or software configuration tool for descriptions of these features and programming labels.

9 Technical Specifications

9 Technical Specifications

The following table contains Physical and Performance Characteristics, User Environment and Regulatory information.

Item	Description
Physical Characteristics	
Dimensions	Height 163 mm Length 91 mm Width 41 mm
Weight (without cable)	Approximately 5.1 ounces/145 g
Electrical Characteristics	
Voltage & Current	Input Voltage: 4.5 - 14.0VDC Operating (typical): 140mA Operating (max): 380mA Idle/standby (typical): 50mA
Performance Characteristics	
Light Source	LEDs
Roll (Tilt) Tolerance	Up to $\pm 360^\circ$
Pitch Tolerance	$\pm 65^\circ$
Skew (Yaw) Tolerance	$\pm 60^\circ$
Print Contrast Minimum	25% minimum reflectance

Depth of Field (Typical)^a	
Symbology	
Code 39	5mil: 0.5 - 15cm 10mil: 0 - 22cm 20mil: up to 40cm
EAN	7.5mil: 0 - 15cm 13mil: 0.5 - 35cm
PDF-417	6.6mil: 1.0 - 130cm 10mil: 0 - 21cm 15mil: 0.5 - 24cm
DataMatrix	10mil: 1.0 - 13 cm 15mil: 0 - 18cm
QR Code	10mil: 0.5 - 13cm 15mil: 0 - 18cm
Minimum Element Width	Standard Range: 1D Min Resolution = 4 mil PDF-417 Min Resolution = 5 mil Datamatrix Min Resolution = 7.5 mil

- a. 13 mils DOF based on EAN. All other 1D codes are Code 39. All labels grade A, typical environmental light, 20°C, label inclination 10°

9 Technical Specifications

Decode Capability	
<p style="text-align: center;">1D Barcodes</p> <p>UPC/EAN/JAN (A, E, 13, 8); UPC/EAN/JAN (including P2 /P5); UPC/EAN/JAN (including; ISBN / Bookland & ISSN); UPC/EAN Coupons; Code 39 (including full ASCII); Code 39 Trioptic; Code39 CIP (French Pharmaceutical); LOGMARS (Code 39 w/ standard check digit enabled); Danish PPT; Code 32 (Italian Pharmacode 39); Code 128; Code 128 ISBT; Interleaved 2 of 5 ; Standard 2 of 5; Interleaved 2 of 5 CIP (HR); Industrial 2 of 5; Discrete 2 of 5; Matrix 2 of 5; IATA 2of5 Air cargo code; Code 11; Codabar; Codabar (NW7); ABC Codabar; EAN 128; Code 93 ; MSI; PZN; Plessey; Anker Plessey; GS1 DataBar Omnidirectional; GS1 DataBar Limited; GS1 DataBar Expanded; GS1 DataBar Truncated; DATABAR Expanded Coupon.</p>	
<p style="text-align: center;">2D / Stacked Codes</p> <p>The BVS HS-QC is capable of decoding the following symbologies using multiple frames (i.e. Multi-Frame Decoding):</p> <p>Datamatrix; Inverse Datamatrix; Datamatrix is configurable for the following parameters:; Normal or Inverted; Square or Rectangular Style; Data length (1 - 3600 characters); Maxicode; QR Codes (QR, Micro QR and Multiple QR Codes); Aztec; Postal Codes - (Australian Post; Japanese Post; KIX Post; Planet Code; Postnet; Royal Mail Code (RM45CC); Intelligent Mail Barcode (IMB); Sweden Post; Portugal Post); LaPoste A/R 39; PDF-417; MacroPDF; Micro PDF417; GS1 Composites (1 - 12); GS1 DataBar Stacked; GS1 DataBar Stacked Omnidirectional; GS1 DataBar Expanded Stacked; GS1 Databar Composites; Chinese Sensible Code; Inverted 2D codes.</p> <p>Note: The SW can apply the Normal/Reverse Decoding Control to the following symbologies: Datamatrix, QR, Micro QR, Aztec and Chinese Sensible Code.</p>	
Interfaces Supported	RS-232, USB Com Std., USB Keyboard, USB OEM
User Environment	
Operating Temperature	0° to 50° C
Storage Temperature	-40° to 70 °C
Humidity	Operating: 0% to 95% relative humidity, non-condensing
Drop Specifications	Reader withstands 18 drops from 1.5 meters to concrete
Ambient Light Immunity	Up to 86,000 Lux
Contaminants Spray/rain Dust/particulates	IEC 529-IP42
ESD Level	16 KV

9

Technical Specifications

Regulatory	
Electrical Safety	UL 60950, CSA C22.2 No. 60950, IEC 60950
EMI/RFI	North America (FCC) : Part 15 Class B; Canada (IC) : ICES-003 Class B; Russia (EAC); European Union EMC Directive; VCCI-Japan; Korean KCC; Taiwan EMC (BSMI); Australia (ACMA); Mexico (NOM)

10 LED and Beeper Indications

10 LED and Beeper Indications

The reader's beeper sounds and its top multi-colour LED illuminates to indicate various functions or errors on the reader. The green LED Spot backprojected on the code provides a reliable feedback to the user. The following tables list these indications. One exception to the behaviors listed in the tables is that the reader's functions are programmable, and so may or may not be turned on. For example, certain indications such as the power-up beep can be disabled using programming barcode labels.

Indicator	Description	LED	Beeper
Power-up Beep	The reader is in the process of powering-up.		Reader beeps four times at highest frequency and volume upon power-up.
Good Read Beep	A label has been successfully scanned by the reader.	LED behavior for this indication is configurable via the feature "Good Read: When to Indicate" (see the OPM for information.)	The reader will beep once at current frequency, volume, mono/bi-tonal setting and duration upon a successful label scan.
ROM Failure	There is an error in the reader's software/programming	Flashes	Reader sounds one error beep at highest volume.
Limited Scanning Label Read	Indicates that a host connection is not established.	N/A	Reader 'chirps' six times at the highest frequency and current volume.
Reader Active Mode	The reader is active and ready to scan.	The LED is lit steadily ^a	N/A
Reader Disabled	The reader has been disabled by the host.	The LED blinks continuously	N/A
Green LED Spot ^a flashes momentarily	Upon successful read of a label, the software shall turn the green spot on for the time specified by the configured value.	N/A	N/A

^a Except when in sleep mode or when a Good Read LED Duration other than 00 is selected

10 LED and Beeper Indications

Programming Mode - The following indications ONLY occur when the reader is in Programming Mode.

INDICATION	DESCRIPTION	LED	BEEPER
Label Programming Mode Entry	A valid programming label has been scanned.	LED blinks continuously	Reader sounds four low frequency beeps.
Label Programming Mode Rejection of Label	A label has been rejected.	N/A	Reader sounds three times at lowest frequency and current volume.
Label Programming Mode Acceptance of Partial Label	In cases where multiple labels must be scanned to program one feature, this indication acknowledges each portion as it is successfully scanned.	N/A	Reader sounds one short beep at highest frequency and current volume.
Label Programming Mode Acceptance of Programming	Configuration option(s) have been successfully programmed via labels and the reader has exited Programming Mode.	N/A	Reader sounds one high frequency beep and 4 low frequency beeps followed by reset beeps.
Label Programming Mode Cancel Item Entry	Cancel label has been scanned.	N/A	Reader sounds two times at low frequency and current volume.

11

Error Codes

11 Error Codes

Upon startup, if the reader sounds a long tone, this means the reader has not passed its automatic Selftest and has entered FRU (Field Replaceable Unit) isolation mode. If the reader is reset, the sequence will be repeated. Press and release the trigger to hear the FRU indication code.


The following table describes the LED flashes/beep codes associated with an error found.

Number of LED Flashes/Beeps	Error	Corrective Action
1	Configuration	Contact Helpdesk for assistance
2	Interface PCB	
6	Digital PCB	
11	Imager	

12 Cleaning

12 Cleaning

Exterior surfaces and scan windows exposed to spills, smudges or debris require periodic cleaning to ensure best performance during scanning.



Use a soft, dry cloth to clean the product. If the product is very soiled, clean it with a soft cloth moistened with a diluted non-aggressive cleaning solution or diluted ethyl alcohol.



CAUTION

Do not use abrasive or aggressive cleansing agents or abrasive pads to clean scan windows or plastics.

Do not spray or pour liquids directly onto the unit.

13 Regulatory Addendum

13 Regulatory Addendum

©2014-2015 Datalogic ADC, Inc. All rights reserved. Datalogic and the Datalogic logo are registered trademarks of Datalogic S.p.A. in many countries, including the U.S.A. and the E.U.

13 Regulatory Addendum

Datalogic ADC, Inc.
959 Terry Street
Eugene, OR 97402 USA
Telephone: (541) 683-5700
Fax: (541) 345-7140

©2014-2015 Datalogic ADC, Inc.

All rights reserved. No part of the contents of this documentation or the procedures described therein may be reproduced or transmitted in any form or by any means without prior written permission of Datalogic ADC, Inc. or its subsidiaries or affiliates ("Datalogic" or "Datalogic ADC"). Owners of Datalogic products are hereby granted a non-exclusive, revocable license to reproduce and transmit this documentation for the purchaser's own internal business purposes.

Purchaser shall not remove or alter any proprietary notices, including copyright notices, contained in this documentation and shall ensure that all notices appear on any reproductions of the documentation. All contact should be to us.

Disclaimer

Datalogic has taken reasonable measures to provide information in this manual that is complete and accurate, however, Datalogic reserves the right to change any specification at any time without prior notice.

Datalogic and the Datalogic logo are registered trademarks of Datalogic S.p.A. in many countries, including the U.S.A. and the E.U. Quicksan is a registered trademark of Datalogic ADC Inc. in many countries, including the U.S.A. and the E.U. All other brand and product names may be trademarks of their respective owners.

Patents

See www.patents.datalogic.com for patent list.

This product is covered by one or more of the following patents:

Design patents: EP002158717, USD723563, ZL201330271434.1

Utility patents: EP0996284B1, EP0997760B1, EP0999514B1, EP1128315B1, EP1396811B1, EP1413971B1, EP1828957B1, JP4435343B2, US6478224, US6512218, US6513714, US6561427, US6808114, US6997385, US7053954, US7075663, US7234641, US7387246, US7721966, US8245926, US8561906

13 Regulatory Addendum

13.1 Regulatory Information

All models are designed to be compliant with rules and regulations in locations they are sold and will be labeled as required.

Any changes or modifications to equipment, not expressly approved by Datalogic or Balluff void the user's authority to operate the equipment.

Statement of Agency Compliance

This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) this device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

FCC Class B Compliance Statement

This equipment has been tested and found to comply with the limits for a Class B digital device pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses, and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna.
- Increase the separation between the equipment and receiver.
- Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.
- Consult the dealer or an experienced radio or television technician for help

Canadian Notice

This equipment does not exceed the Class B limits for radio noise emissions as described in the Radio Interference Regulations of the Canadian Department of Communications.

Le présent appareil numérique n'émet pas de bruits radioélectriques dépassant les limites applicables aux appareils numériques de la classe B prescrites dans le Règlement sur le brouillage radioélectrique édicté par le ministère des Communications du Canada.



CAUTION

Do not attempt to open or otherwise service any components in the optics cavity. Opening or servicing any part of the optics cavity by unauthorized personnel may violate safety regulations.

13 Regulatory Addendum

Customs Union

The CU conformity certification has been achieved; this allows the Product to bear the Eurasian mark of conformity.



13.2 Power Supply

This device is intended to be connected to a UL Listed/CSA Certified computer which supplies power directly to the reader or else be supplied by UL Listed/CSA Certified Power Unit marked "Class 2" or LPS power source rated 5-14V minimum 900mA.

QD2430 can be powered by either a 5V or 12V power supply.

Argentina Power Supply Statement



Atencio

Características de la fuente de alimentación eléctrica.

	5V
Entrada:	350 mA, 50-60 HZ
Salida:	5VDC, 2.5A (-)Negativo al



	12 V
Entrada:	100 -240 Vca 600 mA, 50-60 HZ
Salida:	12VDC, 1500mA (-)Negativo al



Utilice en su red solo fuentes certificadas en Argentina.


El uso de fuentes de alimentación no compatibles puede resultar en riesgo de incendio o de choque eléctrico para el usuario.

13 Regulatory Addendum

13.3 Imager Labeling

Sample labels are shown here to illustrate their location only. Please view the labels on your product for actual details, as they may vary from those depicted.

Scanner Regulatory Label



The QD2430 Handheld Reader is not user-serviceable. Opening the case of the unit can cause internal damage and will void the warranty.

CAUTION

13 Regulatory Addendum

13.4 WEEE Statement

	Waste Electrical and Electronic Equipment (WEEE) Statement
--	--

English

Our BVS HS-P and BVS HS-Q series handheld readers are only intended for commercial use as B2B devices as per the WEEE Directive. The WEEE Directive, valid across the EU, is a standard defining how waste electrical equipment has to be handled.

For you, this means that the handheld readers must not be disposed of in normal household waste or taken to a collection point of public waste disposal authorities.

In the event of disposal, you can return the handheld reader to us.

We will then ensure it is recycled in accordance with the applicable legal requirements.

For your return shipment, please use our RMA process, which you will find on our website.

We are unable to reimburse costs for shipping/packaging.

If the handheld reader to be returned is type BVS HS-QB or BVS HS-PB, the internationally valid shipping regulations for lithium-ion batteries must be observed.

German

Unsere Handheld Reader der BVS HS-P bzw. BVS HS-Q Baureihe sind ausschließlich für den gewerblichen Gebrauch vorgesehen als sog. B2B-Geräte gemäß der WEEE-Richtlinie.

Die EU-weit gültige WEEE-Richtlinie definiert einheitlich wie Elektro-Altgeräten behandelt werden müssen.

Für Sie bedeutet das, dass die Handheld Reader weder über den normalen Hausmüll entsorgt, noch bei einer Sammelstelle eines öffentlich-rechtlichen Entsorgungsträger abgegeben werden dürfen.

Im Falle einer Entsorgung können Sie die Handheld Reader an uns zurücksenden.

Wir stellen dann die Verwertung nach den jeweils geltenden gesetzlichen Vorschriften sicher.

Für die Rücksendung verwenden Sie bitte unseren RMA-Prozess, den Sie auf unserer Webseite finden.

Die Kosten für Versand/Verpackung können wir nicht erstatten.

Falls der zurückzusendende Handheld Reader vom Typ BVS HS-QB oder BVS HS-PB ist, sind die international gültigen Versandvorschriften für Lithium-Ionen-Batterien zu beachten.

China RoHS Table of Restricted Elements

China RoHS

PART	部件名称	Lead (Pb)	Mercury (Hg)	Cadmium (Cd)	Hexavalent Chromium (Cr(VI))	Polybrominated biphenyls (PBB)	Polybrominated diphenyl ethers (PBDE)
		铅	汞	镉	六价铬	多溴联苯	多溴二苯醚
Printed Circuit Board Assembly	电路板组件	X	O	O	O	O	O
Assy, Optics Block	光学组件	X	O	O	O	O	O
Assy, Module	光学组件	X	O	O	O	O	O

有毒有害物质或元素

O: 代表此种部件的所有均质材料中所含的该种有毒有害物质均低于中华人民共和国信息产业部所颁布的《电子信息产品中有毒有害物质的限量要求》(SJ/T 11363-2006) 规定的限量。

X: 代表此种部件所用的均质材料中,至少有一类材料其所含的有毒有害物质高于中华人民共和国信息产业部所颁布的《电子信息产品中有毒有害物质的限量要求》(SJ/T 11363-2006) 规定的限量

13 Regulatory Addendum

13.5 DECLARATION OF CONFORMITY



**Datalogic ADC Srl, Via S. Vitalino, 13
Lippo di Calderara di Reno (BO) 40012 Italy**

EC-085
Rev.: 0
Pag.: 1 di 1

La presente dichiarazione di conformità è rilasciata sotto la responsabilità esclusiva di Datalogic ADC Srl per:

This Declaration of Conformity is issued under the sole responsibility of Datalogic ADC Srl for:

Cette déclaration de conformité est établie sous la seule responsabilité de Datalogic Srl pour:

Diese Konformitätserklärung wird unter der alleinigen Verantwortung des Datalogic ADC Srl erteilt für:

Esta declaración de conformidad se expide bajo la exclusiva responsabilidad de Datalogic ADC Srl para:

QUICKSCAN QD2430

*e tutti i suoi modelli
and all its models
et tous ses modèles
und seine Modelle
y todos sus modelos*

sono conformi alle Direttive del Consiglio Europeo sottoelencate:

are in conformity with the requirements of the European Council Directives listed below:

sont conformes aux spécifications des Directives de l'Union Européenne ci-dessous: den nachstehenden angeführten Direktiven des Europäischen Rats:

cumple con los requisitos de las Directivas del Consejo Europeo, según la lista siguiente:

2004/108/EC - EMC Directive

2011/65/EU – RoHS Directive

Basate sulle legislazioni degli Stati membri in relazione alla compatibilità elettromagnetica ed alla sicurezza dei prodotti.

On the approximation of the laws of Member States relating to electromagnetic compatibility and product safety.

Basée sur la législation des Etats membres relative à la compatibilité électromagnétique et à la sécurité des produits.

Über die Annäherung der Gesetze der Mitgliedsstaaten in bezug auf elektromagnetische Verträglichkeit und Produktsicherheit entsprechen.

Basado en la aproximación de las leyes de los Países Miembros respecto a la compatibilidad electromagnética y las Medidas de seguridad relativas al producto.

Questa dichiarazione è basata sulla conformità dei prodotti alle norme seguenti:

This declaration is based upon compliance of the products to the following standards:

Cette déclaration repose sur la conformité des produits aux normes suivantes:

Diese Erklärung basiert darauf, daß das Produkt den folgenden Normen entspricht:

Esta declaración se basa en el cumplimiento de los productos con las siguientes normas:

**EN 55022 (CLASS B ITE),
DECEMBER 2010:**

INFORMATION TECHNOLOGY EQUIPMENT - RADIO DISTURBANCE CHARACTERISTICS - LIMITS AND METHODS OF MEASUREMENT

EN 55024, NOVEMBER 2010:

INFORMATION TECHNOLOGY EQUIPMENT - IMMUNITY CHARACTERISTICS - LIMITS AND METHODS OF MEASUREMENT

EN 50581, SEPTEMBER 2012:

TECHNICAL DOCUMENTATION FOR THE ASSESSMENT OF ELECTRICAL AND ELECTRONIC PRODUCTS WITH RESPECT TO THE RESTRICTION OF HAZARDOUS SUBSTANCES

**LIPPO DI CALDERARA,
NOVEMBER 25TH , 2013**

**Ruggero Cacioppo
Quality Assurance Manager**

14 Ergonomic Recommendations

14 Ergonomic Recommendations



CAUTION

In order to avoid or minimize the potential risk of ergonomic injury follow the recommendations below. Consult with your local Health & Safety Manager to ensure that you are adhering to your company's safety programs to prevent employee injury.

- Reduce or eliminate repetitive motion
- Maintain a natural position
- Reduce or eliminate excessive force
- Keep objects that are used frequently within easy reach
- Perform tasks at correct heights
- Reduce or eliminate vibration
- Reduce or eliminate direct pressure
- Provide adjustable workstations
- Provide adequate clearance
- Provide a suitable working environment
- Improve work procedures.

14.1 Services and Support

Balluff provides several services as well as technical support through its website. Log on to www.Balluff.com and click on the links indicated for further information.

Products

Search through the links to arrive at your product page where you can download specific Manuals & Documentation, Data Sheets, Product Catalogues, etc..

Service & Support

- **Technical Support** - Return Material Authorization (RMA) Repairs.
- **Downloads** – download Brochures and Catalogues

Contact Us

- Information Request Form and Sales & Service Network

Notes

Notes

 **www.balluff.com**

**World Headquarters
Germany**

Balluff GmbH
Schurwaldstraße 9
73765 Neuhausen a.d.F.
Deutschland
Tel. +49 7158 173-0
Fax +49 7158 5010
balluff@balluff.de
 www.balluff.com

**Subsidiaries
USA**

Balluff Inc.
8125 Holton Drive
Florence,
Kentucky 41042-0937
Phone (859) 727-2200,
1-800-543-8390
applications@balluff.com